



Commercial status

End-of-Sale Notice : JUN 01, 2021

 End-of-Sale Notice

Main

Range of product	Harmony XB5R
Product or component type	Wireless and batteryless transmitter
Device short name	XB5R
Bezel material	Dark grey plastic
Mounting diameter	40 Mm
Sale per indivisible quantity	1
Shape of signaling unit head	Round
Type of operator	Spring return
Operator profile	Black mushroom Ø 40 mm, unmarked

Complementary

CAD overall width	56 Mm
CAD overall height	52.59 Mm
CAD overall depth	150.2 Mm
Mechanical durability	1000000 Cycles
Product compatibility	ZBZ28
Mechanical robustness	Free fall resistance 1000 mm conforming to EN/IEC 60068-2-32
Compatibility code	XB5R

Environment

Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
IP degree of protection	IP65 (front face) conforming to IEC 60529 IP30 (back face) conforming to IEC 60529 IP65 (front face) conforming to UL Type 12
NEMA degree of protection	NEMA 12
IK degree of protection	IK03 conforming to IEC 50102
Product certifications	DNV CSA GL LROS (Lloyds register of shipping) UL listed BV
Vibration resistance	+/- 10 mm (f= 2...11 Hz) conforming to IEC 60068-2-6

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commercialisation**