

Products Low Voltage Products and Systems Industrial Plugs and Sockets Plugs & Sockets Surface Inlets

General Information

Extended Product Type:	232BS6
Product ID:	2CMA193314R1000
EAN:	7392696933148
Catalog Description:	Surface inlet, 6h, 32A, IP44, 2P+E
Long Description:	Surface Inlet, earthing sleeve position 6h, rated current 32A, IP44 splashproof, 2-poles+earth, frequency 50-60 Hz, color code Blue

Additional Information

Additional Information:	2P+E
Cable Cross-Section:	2.5 ... 10 mm ²
Cable Diameter:	22 mm
Color:	Blue
Country of Origin:	Czech Republic (CZ)
Customs Tariff Number:	85366990
Data Sheet, Technical Information:	2CMC700014C0008
Declaration:	2CMC700005D0001
Declaration of Conformity - CE:	2CMC700005D0001
Degree of Protection:	IP44
E-nummer:	2417180
EAN:	7392696933148
ETIM 4:	EC001319 - CEE plug for mounting on machines and equipment
ETIM 5:	EC000140 - CEE plug
ETIM 6:	EC001319 - CEE plug for mounting on machines and equipment
Enclosure Material:	Thermoplastic
Environmental Information:	2CMC700001D0002
Frequency (f):	60 Hz
Function:	Surface inlet
Gross Weight:	0.27 kg
Housing Material:	Plastic (PA)
IIT Publishing Status:	Level 0 - Information enabled
Instructions and Manuals:	2CMC700002D0001
Invoice Description:	Ind. P&S#232BS6
Minimum Order Quantity:	10 piece
Number of Poles:	3
Object Classification Code:	2CMT005069
Package Level 1 EAN:	7392696663144
Package Level 1 Gross Weight:	4.4 kg
Package Level 1 Height:	428 mm
Package Level 1 Length:	175 mm
Package Level 1 Units:	10 piece
Package Level 1 Width:	188 mm
Product Main Type:	EBS
Product Name:	Industrial Surface Inlet
Product Net Depth:	153 mm
Product Net Height:	85 mm

Product Net Length:	153 mm
Product Net Weight:	0.44 kg
Product Net Width:	94 mm
Protection Type:	Splashproof
Rated Current (I_n):	32 A
Rated Voltage (U_r):	200 ... 250 V
RoHS Date:	L23
RoHS Information:	2CMC700057D0001
RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
Selling Unit of Measure:	piece
Short Description:	Surface inlet, 6h, 32A, IP44, 2P+E
Size:	94X85X155
Standards:	IEC 60309-1 IEC 60309-2
Suitable For:	Surface Inlets
Suitable for Product Class:	Industrial Plugs and Sockets
UNSPSC:	39120000
Clock Position Of Grounding Contact:	6 hour

