



RECOMMENDED P.C.B LAYOUT (TOP VIEW)
TOLERANCES: ±0.10mm

POSITION	A	B	C
14F	25.20	36.00	43.90
24F	36.00	46.80	54.70
36F	46.90	59.70	67.70
50F	64.10	74.90	82.80

MATERIAL & FINISHES

- INSULATOR - F.B.T. FIBERGLASS FIBER
 UL 94V-0
 CONTACT - PHOSPHOR BRONZE
 SHELL FINISH - STEEL NICKEL PLATED
 HOUS - STEEL
 CONTACT PLATING - CONTACT
 1. GOLD FLASH COMPLETED
 2. SELECTIVE GOLD OVER NICKEL PLATED
 CONTACT AREA (TOP OVER NICKEL PLATED (TAB AREA)
 - SHELL
 NICKEL OVER COPPER PLATED
 - HOUS
 NICKEL OVER COPPER PLATED

ELECTRICAL CHARACTERISTICS

- RATING CURRENT : 5 AMP
 CONTACT RESISTANCE : < 10 MILLIOHM
 INSULATION RESISTANCE : > 1000 MEGOHM AT 500V
 DIELECTRIC VOLTAGE : 1800V AT 1 MINUTE
 OPERATION TEMPERATURE : -55°C TO +100°C

APPLIED TO WAVE SOLDER CAPABLE TO 240°

TABEL:

PART NO	ITEM NO	No of Pins
238-1156	G57LE14F	14
238-1162	G57LE24F	24
238-1178	G57LE36F	36
238-1184	G57LE50F	36

僅供參考



REACH
RoHS

SUBSTITUTIONS PERMITTED		REVISIONS		DATE	
REVISIONS		DATE		DATE	
REV	BY	REV	BY	REV	BY
1	Eric	1	Eric	1	Eric
2	Mark	2	Mark	2	Mark
PART NO: 238-1162		REV: 2		DATE: 2018-09-21	