

 SWITCHING POWER SUPPLY	<b>PRODUCT SPECIFICATION</b>	File: EF-300SFD-80-6
	Model:SS-300SFD Active PFC Full Range Revision: 1.3	Date: Aug. 3, 2006 Page: 1 of 5

<b>1. SCOPE</b>	2
<b>2. AC INPUT and AC OUTPUT</b>	2
<b>3. DC OUTPUT CURRENT LOAD RANGES</b>	2
3.1 DC OUTPUT CURRENT RATINGS	2
3.2 CROSS REGULATION	3
3.3 OUTPUT RIPPLE and NOISE	3
3.4 DYNAMIC DC OUTPUT CHARACTERISTICS	3
3.5 DC OUTPUT ON/OFF CONTROL	3
<b>4. OUTPUT PROTECTION</b>	4
4.1 TOTAL POWER PROTECTION	4
4.2 OVER VOLTAGE PROTECTION	4
4.3 SHORT CIRCUIT PROTECTION	4
4.4 RESET AFTER SHUTDOWN	4
<b>5. POWER GOOD SIGNAL</b>	4
<b>6. EFFICIENCY</b>	4
6.1 80 PLUS Specification	4
6.2 ENERGY STAR MODE	4
6.3 STANDBY MODE	4
<b>7. COOLING OF PSU</b>	5
<b>8. ACTIVE POWER FACTOR CORRECTION (PFC)</b>	5
<b>9. ENVIRONMENT</b>	5
9.1 OPERATING	5
9.2 SHIPPING / STORAGE	5
<b>10. MTBF</b>	5
<b>11. EMC</b>	5
<b>12. SAFETY</b>	5
<b>13. MECHANICAL DRAWING</b>	5

 SWITCHING POWER SUPPLY	<b>PRODUCT SPECIFICATION</b>	File: EF-300SFD-80-6
	Model:SS-300SFD Active PFC Full Range Revision: 1.3	Date: Aug. 3, 2006 Page: 2 of 5

### 1. SCOPE

This specification defines electrical performance and characteristic of “**SS-300SFD Active PFC**” Full Range power supplies which 80Plus certified.

### 2. AC INPUT and AC OUTPUT:

Limits	RANGE(100-240VAC) <sup>1</sup>		Unit
	Minimum	Maximum	
AC Input voltage	90	264	Vac
AC Input frequency	47	63	Hz
AC Input Current		5	Amp(rms)
Inrush current <sup>2</sup> (cold)		100	Amp(peak)
Inrush current (warm)	NO COMPONENT OVER STRESSED.		
	NO FUSE BLOW.		
	NO DAMAGE TO THE POWER SUPPLY.		

NOTE: 1. The AC input is protected by the AC fuse.  
 2. Measured at 25 Deg C Ambient.

### 3. DC OUTPUT REQUIREMENTS:

#### 3.1 DC OUTPUT CURRENT RATINGS

DC OUPTUT		Tolerance
Group1	+3.3VDC	+5%/-5%
	+5VDC	+5%/-5%
	+12VDC	+5%/-5%
	-12VDC	+10%/-10%
Group2	+5Vsb	+5%/-5%

Load Range Output	Minimum Load	Maximum Load	Peak Load
+12V1	1A	8A	10A
+12V2	1A	14.5A	X
+5V	0.5A	20A	X
+3.3V	0.3A	20A	X
-12V	0A	0.8A	X
+5Vsb	0A	2A	2.5A

1. Maximum continuous total DC output power should not exceed 300 W
2. Maximum continuous combined load on +3.3 VDC and +5 VDC outputs should not exceed 125 W/28A
3. Maximum peak total DC output power should be approximate 330 W.
4. Peak power and current loading should be supported for a minimum of 1 second
5. The total power will derate from 100% to 90% linearly when ac input 100v to ac 90v.

### 3.2 CROSS REGULATION

The +5V & +3.3V combined load and +12VDC load shall remain within the Defined in section 3.1 over cross load combinations shown Figure 1




Figure 1 +5V&+3.3V , +12V Output Cross Load Combinations

### 3.3 OUTPUT RIPPLE and NOISE

Measurement is made with an oscilloscope with 20 MHz bandwidth. Output should be at the connector with a 0.1uF ceramic disk capacitor and a 10uF electrolytic capacitor simulate system load. The length of ground wire on probe should not longer than non-differential type of scope was used.


+3.3V	+5V	+12V	-12V	+5Vsb
50mV	50mV	120mV	150mV	50mV

### 3.4 DYNAMIC DC OUTPUT CHARACTERISTICS

+/-10% Max. Excursion for 50% to 100%, or 100% to 50% load change with return to Regulation in 0.5 mS.

### 3.5 DC OUTPUT ON/OFF CONTROL

A low active PS-ON (DC ON/OFF) input signal is equipped, which provide the interface **ENABLE** or to **DISABLE** the **GROUP1** of DC output. This signal is electrically to interface with **TTL, OPEN COLLECTOR** and the **HARD SWITCH**.



SIGNAL NAME		MAXIMUM	MINIMUM
T1	+5V RISE TIME	20 mS	
T2	+5V TURN-ON DELAY TIME	100 mS	

 SWITCHING POWER SUPPLY	<b>PRODUCT SPECIFICATION</b>	File: EF-300SFD-80-6
	Model:SS-300SFD Active PFC Full Range Revision: 1.3	Date: Aug. 3, 2006 Page: 4 of 5

T3	PWR_OK DELAY TIME	500 mS	100 mS
T4	DC SAVE TIME		1 mS
T5	HOLD-ON TIME (AT NOMINAL AC INPUT)		12 mS

#### 4. OUTPUT PROTECTION

##### 4.1 TOTAL POWER PROTECTION: ( OPP )

Total power 135% max with shut-down and latch off protection.

##### 4.2 OVER VOLTAGE PROTECTION: ( OVP )

OVER VOLTAGE	ACTIVE RANGE		RESULT
	Min.	Max.	
+3.3V	3.76V	4.8V	Shutdown&Latch OFF The Group 1 DC Output
+5V	5.7V	7.0V	
+12V		15.6V	

##### 4.3 SHORT CIRCUIT PROTECTION: ( SCP )

The short between any output of group 1 will shut down all group1.

The short at group 2 will Shut down both group 1 and group 2.

##### 4.4 RESET AFTER SHUTDOWN

Whenever the power supply latches into shutdown state due to fault condition on its

The power supply will return to normal operation only after the fault has been removed

and the power switch has been cycled off/on with **A MINIMUM OFF TIME OF 20mS.**  
(PS-ON)

#### 5. POWER GOOD SIGNAL:

Signal Type: open collector +5DC, TTL compatible.

Logic Level: <0.4V while sinking 4 mA.

Logic Level High: between 2.4VDC and +5V output while sourcing 200 uA.

#### 6. EFFICIENCY:

##### 6.1 80 PLUS Specification:

Over 80% at normal input voltage(AC 115V 60Hz or AC 230V 50Hz) when 20%,50%,100% loading.

##### 6.2 ENERGY STAR MODE

Over 50% at 30W max power consumption with 15.0W load or more delivered to DC

##### 6.3 STANDBY MODE

During measurement of the "STANDBY MODE" condition, the main converter is off (PS\_ON=High). +5Vsb converter is working and standby input power is measured.

true RMS input power (standby) +5Vsb/ 0.5A; input voltage: 230VAC	< 5.5W
true RMS input power (standby) +5Vsb/ 0A ; input voltage: 230VAC	< 2.0W

**7. COOLING OF PSU**

A DC FAN was equipped to cooling the power supply and system load , the FAN will draw in air from system into PSU directly, and exhaust air through vent hole in AC receptacle side.

Fan parameters

Rated voltage	12VDC
Dimensions	80*80*25 (mm)
Air flow	30 CFM min.
Noise	<35 dBA

**8. ACTIVE POWER FACTOR CORRECTION (PFC):**

**8.1** Harmonic current meets IEC1000-3-2 / EN61000-3-2 standards.

**8.2** PFC>0.95 ; 220Vac input >0.98(typical) under full load.

**9. ENVIRONMENT**

**9.1 OPERATING**

Temperature: 0 to 50 °C. (The rated power will derate from 100% to 80% from 40°C to Linearly)

Relative Humidity: 20% to 85%

**9.2 SHIPPING / STORAGE**

Temperature: -40 to 85 Deg C

Relative Humidity: 10% to 95%

**10 MTBF**

Over 100,000 hours at 75% Load and 25°C ambient conditions and 115V~ or 230V~ input excluding the DC Fan.

**11 EMC**

Comply to CE EN50081-1(1992) , EN55024(1998) & FCC (B) regulation,C Tick

**EMS**

Comply to EN55024(1998)

**HARMONIC DISTORTION**

Comply to EN61000-3-2(2000)

**12 SAFETY:**

Conform to IEC950 (EN60950) standards: TUV, CB, C-UL , S

**13 MECHANICAL DRAWING:**

Dimension : L125\*W100\*H76.84 mm