

Technical data


1312SC3

Double-row self-aligning ball bearings



Self-aligning ball bearing, pressed steel cage, open

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	60 mm
D - External diameter	130 mm
B - Bearing/Inner ring width	31 mm
rs - Min fillet radius	2,1 mm
Radial clearance class	C3
Precision class	P0
Mass	2 kg

PRODUCT PERFORMANCE

C - Dynamic load	57500000 mN
C0 - Static load	20800000 mN
Cu - Fatigue limit load	510000 mN
e - Coefficient	0.23
Y0 - Static axial load coefficient	2.9
Y1 - Lower axial load coefficient	2.8
Y2 - Upper axial load coefficient	4.3
N lim - Oil lubrication limit speed	33600 °/s
N lim - Grease lubrication limit speed	27000 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	71 mm
Da max - Max shoulder diameter OR	119 mm



1312SC3
Double-row self-aligning ball bearings

ABUTMENT	
ra max - Max shaft & housing fillet radius	2 mm

