



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Header**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board**

Number of Positions: **2**

Centerline (Pitch): **3 mm [.118 in]**

Features

Product Type Features

Header Type	Fully Shrouded
Rectangular Power Connector Type	Header
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	2
PCB Mount Orientation	Right Angle
Number of Power Positions	2
Number of Signal Positions	0
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------



Contact Features

Contact Layout	Inline
Multiple Contact Types	Without
Contact Current Rating (Max)	5 A
Contact Retention Within Housing	Without
Contact Type	Pin
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	2.54 µm[100 µin]
Contact Termination Area Plating Thickness	2.54 µm[100 µin]

Termination Features

Termination Post & Tail Length	1.4 mm[.055 in]
Termination Method to Printed Circuit Board	Surface Mount

Mechanical Attachment

Strain Relief	Without
Mating Alignment Type	Polarization
Mating Alignment	With
Panel Mount Feature	Without
PCB Mount Retention	With
PCB Mount Retention Type	Hold-Down Post
Connector Mounting Type	Board Mount
Mating Retention	With
Mating Retention Type	Locking Tab

Housing Features

Centerline (Pitch)	3 mm[.118 in]
Housing Color	Natural
Housing Material	Nylon

Dimensions

Insulation Diameter (Max)	1.52 mm[.06 in]
PCB Thickness (Recommended)	.06 mm[1.57 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------



Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

CSA Rating	Certified
UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire
Agency/Standard Number	E28476
Agency/Standard	CSA, UL
UL Rating	Recognized
CSA File Number	LR7189
VDE Tested	Yes

Packaging Features

Packaging Method	Box & Tray, Tray
Packaging Quantity	215

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C





Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1445022-2 MICRO MNL RECEPT HSG SINGLE R	 TE Part # 2-1445057-4 MICRO MNL HDR ASSY SINGLE ROW	 TE Part # 2-1445057-3 MICRO MNL HDR ASSY SINGLE ROW	 TE Part # 2008571-2 2 POS MICRO MNL, TOP LATCH, BL
 TE Part # 2029030-2 2P MICRO MNL HDR ASY SR SIDE L	 TE Part # 2-1445057-6 MICRO MNL HDR ASSY SINGLE ROW	 TE Part # 2-1445057-5 MICRO MNL HDR ASSY SINGLE ROW	 TE Part # 2029030-3 3P MICRO MNL HDR ASY SR SIDE L
 TE Part # 2029047-2 2P MICRO MNL RCPT HSG SR SIDE	 TE Part # 2029102-2 2P MICRO MNL RCPT SR SIDE WHT	 TE Part # 2-1445056-2 MICRO MNL HDR ASSY SINGLE ROW	 TE Part # 2008570-2 2 POS MICRO MNL, SIDE LATCH, B
 TE Part # 2029030-4 4P MICRO MNL HDR ASY SR SIDE L	 TE Part # 2029104-3 3P MICRO MNL HDR ASY SR SIDE N	 TE Part # 2029104-4 4P MICRO MNL HDR ASY SR SIDE N	 TE Part # 1-2008570-2 2 POS MICRO MNL, SIDE LATCH, N





TE Part # 1-2008571-2
2 POS MICRO MNL, TOP LATCH, NA



TE Part # 1-2029030-2
2P MICRO MNL HDR ASSY SR SIDE L



TE Part # 2315752-2
2P, MICRO MNL RCPT HSG SINGLE ROW, V0 GW

Also in the Series | Micro MATE-N-LOK



Connector Contacts(1)



Insertion & Extraction Tools(1)




Power Contacts(26)



Rectangular Power Connectors(712)


Customers Also Bought



TE Part #5102159-4
A/L UNIV HDR 20P RA



TE Part #3-640440-2
02P MTA100 CONN ASSY 22AWG RED



TE Part #1761608-9
IDC LOW PRO HDR 26P VERT SHT LAT BLK



TE Part #1909763-1
UMCC MICRO-COAX RECPT GEN 1 HIGHER LEVEL



TE Part #2-520194-2
ULTRAFast 187 ASSY REC 22-18 TPBR LP



TE Part #350428-1
02P UMNL PIN HDR ASSY NATL



TE Part #5-2337992-8
RJ45 JACK MAG. POE 1GB LED 1X1



TE Part #CF7300-000
HF-17FRX4



TE Part #1878651-5
QC101

TE Part #AAC5554-00
100P1447-1-ZK-WR3-PCR12.6



Documents

Product Drawings

2P MICRO MNL HDR ASY SR SIDE N

English

CAD Files

Customer View Model

ENG_CVM_CVM_2029104-2_C.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2029104-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2029104-2_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English

MICRO MATE-N-LOK CONNECTOR SYSTEM

English

1773458-4_MICRO_MATE_N_LOK_CONNECTOR_SYSTEM_QRG

English

LOW_PROFILE_MICRO_M-N-L

English

Product Specifications

Application Specification

English

Agency Approvals

UL

English