



Part Number : [1600260002](#)

Product Description : stAK50h Hybrid Receptacle,
12 Circuits, Key 2, Light Green, Bag

Series Number : 160026

Status : Active

Product Category : Connector Housings



Documents & Resources

Drawings

[1600260002_sd.pdf](#)

[PK-31302-266-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[1600140001-AS-CH-000.pdf](#)

[AS-160014-001-001.pdf](#)

[1600140002-PS-000.pdf](#)

[1600140001-000.pdf](#)

[1600140000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	160026
Description	stAK50h Hybrid Receptacle, 12 Circuits, Key 2, Light Green, Bag
Application	Automotive, Power, Signal, Wire-to-Board
Product Name	stAK50h
UPC	887191923253

Physical

Circuits (maximum)	12
Color - Resin	Green (Light)
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS
Net Weight	5.670/g
Number of Rows	4

Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm, 4.00mm, 5.20mm, 7.20mm
Pitch - Termination Interface	2.00mm, 4.00mm, 5.20mm, 7.20mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +105°C LV-214, -40° to +85°C GMW3191 June2012

Mates With / Use With

Mates with Part(s)

Description	Part Number
stAK50h Vertical Hybrid Header, 12 Circuits, Key 2, Green, Tube	<u>2005010122</u>
stAK50h Right-Angle Hybrid Header, 12 Circuits, Key 2, Green, Tube	<u>2005020122</u>

Use with Part(s)

Description	Part Number
Use With	Aptiv OCS 1.20mm Terminal or JST MSA 1.20mm Terminal, TE AMP MCP 2.80mm Terminal or Aptiv CTS 2.80mm Terminal