

LBE 17-11 125

Variable-speed 1700 watt angle grinder with brake, 125 mm

Order no. 447668

GTIN 4030293197282



- + Microprocessor control with soft start, restart protection after power failure, overload protection, CDC-electronic feedback control
- + With mechanical brake, the tool stops in 3.5 seconds
- + Anti-Kickback - this shuts down the motor on the disc being blocked
- + Highly efficient and resilient motor for more power output
- + Effective cooling and optimised carbon geometry ensure a long service life
- + Extensive dust protection for motor and gears
- + Compact and ergonomic shape
- + Tool-free adjustment of safety guard
- + Lockable slide switch
- + Spindle lock
- + SoftVib handgrip with integrated, patented locknut wrench and vibration damping
- + High-quality, powerful angle grinder for cutting, roughing down, and grinding



Technical data

Power consumption	1700 W
Power output	1050 W
Voltage	230 V
Frequency	50/60 Hz
Max. disc diameter	125 mm
No-load speed	2800 - 11500 rpm
Angle grinder material	M14
Cable length	4.0 m
Dimensions WxLxH	340 x 77 x 105 mm
Weight	2.6 kg

Standard equipment

- 1 Sanding guard (436860)
- 1 SoftVib side handle (530903)
- 1 Clamping flange (335282)
- 1 Clamping nut M 14 (100080)