



PRODUCT NUMBER: 1010925
Viking V1 Multiple-Position Earmuff

[Learn more about our products at howardleight.com](http://howardleight.com)

>

[Learn more about hearing conservation at hearforever.org](http://hearforever.org) >



Overview

Reference Number

1010925

Product Type

Hearing Protection

Range

Earmuffs

Line

Noise Blocking Earmuffs

Brand

Howard Leight by Honeywell

Brand formerly known as

BILSOM

Industry

- Industry • Administration • Agriculture • Army - Defence • ATEX environment
- Automotive and Part Manufacturer • Aviation • Building and Construction • Catering
- Chemical Industries • Energy or Electricity • Fire Protection brigades • Fishing • Food Industries
- Foundry • Glass Industries • Green Spaces • Homeland defense • Industrial Cleaning
- Iron and steel industry • Laboratory • Logistics • Maintenance • Medical and Pharmaceutical
- Metal steel • Mining and Quarrying • Offshore • Paper Industries • Petro-chemical
- Printing Industries • Services • Ship Building • Telecoms • Textile Industries • Transportation
- Utilities • Water treatment • Welding • Wood Industries

Product Use

Noise Blocking Earmuff

Features & Benefits

Feature

Multiple-position headband allows wearer to select position over-the-head, behind-the-head or under-the-chin. Now features Bilsom's patented Air Flow Control™ technology, delivering optimal attenuation across all frequencies, without increasing earcup size or weight. Alternative to cap-mounted earmuffs - wear with hard hats, face shields, respirators

and other PPE. Non-deforming outer headband withstands rough treatment in the toughest workplaces. Snap-in ear cushions make replacement quick and easy. Includes headband strap for better positioning when worn behind-the-head or under-the-chin. Dielectric construction suitable for all workplaces, especially electrical environments.

Benefit

The Viking™ series multiple-position earmuff gives workers flexibility to wear their earmuffs over-the-head, behind-the-head and under-the-chin. Viking earmuffs can be worn with other PPE, including hard hats, visors, face shields, respirators and welding shields. Plus, Viking's robust non-deforming dielectric construction withstands use and abuse, while protecting your workers in electrical environments. NOW FEATURING AIR FLOW CONTROL™ TECHNOLOGY

Technical Description

SNR (dB)

30

H (dB)

32

M (dB)

28

L (dB)

21

Attenuation Data

Frequency (Hz) Frequenz (Hz) Fréquence (Hz)631252505001000200040008000Mean Attenuation (dB) Mittlere Dämmung (dB) Atténuation moyenne (dB)17.914.120.625.832.032.133.734.4Standard Deviation (dB) Standardabweichung (dB) Déviation standard (dB)2.42.33.12.52.82.53.12.5Assumed Protection (dB) Angenommener (dB) Protection supposée (dB)15.511.817.523.329.229.630.631.9

Earmuff Construction

Plastic [or Dielectric]

Other Material

PP webbing, POM, LDPE, PA, EPDM, ABS, PUR-E, PP, PVC

Dielectric

Yes

Color

Black and Light Blue

Batteries Needed

None

Weight (grs)

191

Headband Style

Multiple-Position

Sound Amplification

No

AM/FM Radio

No

Automatic Shut-Off Function

No

Audio Input Jack

No

Hi-Visibility

No

Certifications

 E.C. Declaration of Conformity

EC Category PPE

2

Quality Assurance

ISO 9001 / 2000

EC Certificate Number

1486

EC Attestation

 EC Attestation

EC Attestation Number

060353

 CE Certificate - Viking V1s

http://www.honeywellsafety.com/supplementary/documents_and_downloads/secured/hearing_protection/earmuffs/43788/1033.aspx

Maintenance

Life Cycle

Cushions should be replaced periodically to retain maximum attenuation. Use the following as a guideline for replacement of ear cushions and insert foam. General use and wear - Ear cushions and foam inserts should be replaced at least every 6 months. Heavy use or wear in humid/extreme climates - Ear cushions and foam inserts should be replaced at least every 3 months. Cracking or leakage is visible - replace ear cushions and foam inserts immediately.

Storage Information

When not in use, the earmuffs should be stored in a clean dry container or locker. Do not use solvents or petroleum-based products. Do not immerse the earmuffs in water.

Care Instructions

Earmuffs are an important safety product and should be inspected regularly. Its use, care and maintenance are critical to its effective performance. Earmuffs and in particular ear cushions may deteriorate with use and should be examined at frequent intervals for cracking and leakage. If the ear cushions become hard, damaged or deteriorated, they should be replaced promptly using recommended Hygiene Kits. Earmuffs should be maintained by regular cleaning. Use a mild disinfectant solution. A gentle wipe is all that is required.

Parts & Accessories

Accessories

Hygiene Kit - Packed in a plastic bag, including two ear cushions and two foam pads. Ref. # 1006018 for V1
Beltclip - For carrying purpose. Old Ref. # 1000252 New Ref. # 1016730 Cool II Pads - Sweat absorbing pads. Ref. # 1000365 5-pair, Ref. # 1000364 100-pair
Optisorb - cotton sleeve slides over earcup. Ref. # 3302101
Polar Hood - Ref. # 1016870 Lg/XLg; Ref. # 1016871 Sm/Med

Packaging

EAN Code

7312550109250

EC TYPE-EXAMINATION CERTIFICATE :1486

Product description:-

Ear-muffs

Product identification:-

Bilsom Viking V1s

Manufactured by:-

Bacou-Dalloz AB
Strandbadsvagen 15
252 29 Helsingborg
Sweden

When assessed and examined against harmonised standard EN352-1:2002 is found to be in conformity with Council Directive 89/686/EEC, and associated amendments, relating to personal protective equipment .

Signed

K J Warren, Manager, Certification Services

Date: 19th May 2006

For and on behalf of INSPEC International Ltd. (Notified Body No: 0194)

Terms and Conditions associated with INSPEC
EC Type-Examination Certificate No: 1486

Reference Documents:-

- | | | | |
|------|--------------------------|---|--|
| i) | Test Reports | - | INSPEC 06.003.53 |
| ii) | Technical File | - | INSPEC ref. TF/1486 |
| iii) | Test and Inspection Plan | - | CE Product Certification, Test and Inspection Plan |

Conditions attached to the issue of this certificate:

- i) Marking and instructions have been assessed in the English language only. It is the Manufacturers/Authorised Representatives responsibility to obtain and supply language versions acceptable to the country where the product is to be sold.
- ii) Any changes to the product, technical file or quality manual/quality plan shall be immediately notified to INSPEC.
- iii) The Manufacturer/Authorised Representative shall comply at all times with INSPEC's Regulations governing CE Product Certification.
- iv) This Certificate remains the property of INSPEC and may be withdrawn if any of the conditions attached to its issue are not complied with.

CERTIFICATION SCHEDULE

COMPANY: Bacou-Dalloz AB

CERTIFICATE NO: EC1486

SCHEDULE NO: ONE

DATE: 19th May 2006

Model: Bilsom Viking V1s

Description: B-T-N / O-T-H / U-T-C ear-muff

Size Range: S / M / L

Attenuation Data

Freq. (Hz)	63	125	250	500	1000	2000	4000	8000
Mean att. (dB)	17.9	14.1	20.6	25.8	32.0	32.1	33.7	34.4
Std. Dev. (dB)	2.4	2.3	3.1	2.5	2.8	2.5	3.1	2.5
APV (dB)	15.5	11.8	17.5	23.3	29.2	29.6	30.6	31.9
O-T-H mode:	H = 32dB		M =28 dB		L =21 dB		SNR =30 dB	

Signed for and on behalf of INSPEC.....

Kevin Warren, Manager, Certification Services



E.C. Declaration of Conformity

The manufacturer or its legal representative supplier in the European Community:

Honeywell Safety Products Europe

Declares that the Personal Protective Equipment described here after conforms to the provisions of the European Council Directive 89/686/CEE:

Designation: Viking V1 Multiple-Position Earmuff

Reference: 1010925

Standard(s): EN-352-1:2002

This PPE is the object of the below EC examination certificate n°:

1486

Delivered by:

INSPEC

56 Leslie Hough Way

Salford

M6 6AJ

Greater Manchester

United Kingdom

+44 (0)12 96 68 29 66

Drawn up in Sweden, on the 10/06/2015

By:

Division: Hearing Protection

ZI Paris Nord II 33, rue des Vanesses BP 50288 95958 Roissy CDG France

Tel: +33 (0) 49 90 79 79 Fax: +33 (0)1 49 90 79 80

www.honeywellsafety.com