





Features

- Universal AC input / Full range(up to 305VAC)
- Built-in active PFC function
- · High efficiency up to 95%
- · Fanless design, cooling by free air convection
- -55~+65°C wide operating range
- · Aluminum case and filling with heat-conducted silicone
- · IP65 design, optional IP68 rated model available
- Meet 6KV surge immunity level
- · Withstand 10G vibration test
- Operating altitude up to 5000 meters (Note.7)
- Protections: Short circuit / Overload / Over voltage / Over temperature
- 6 years warranty (Note.10)

IP65 IP68 (optional) PC CBCE


Applications

- Outdoor telecommunication equipment
- · Outdoor electronic signage and billboard
- · Petroleum plant or mine shaft facility

■ Description

HEP-480 is a 480W industrial AC/DC power supply featuring the outstanding capability to operate under highly humid, dusty, oily, and high-vibration harsh environment. The entire series is housed with the aluminum case and fully potted with heat-conducted silicone. Thanks to state-of-the-art design, the working efficiency is up to 95%, enabling HEP-480 perfectly work between -55°C and +65°C under free air convection.

Model Encoding



A : Standard model, IP65, Vo and Io level can be adjusted through internal potentiometer.

Blank: Optional model, IP68, with fixed Vo and Io level.



SPECIFICATION

MODEL		HEP-480-24	HEP-480-36	HEP-480-48	HEP-480-54
	DC VOLTAGE	24V	36V	48V	54V
	RATED CURRENT	20A	13.3A	10A	8.9A
	RATED POWER	480W	478.8W	480W	480.6W
	RIPPLE & NOISE (max.) Note.2		250mVp-p	250mVp-p	350mVp-p
	THI I EE G HOIGE (Maxi) Hotel	Adjusted for A-type only (via built-in potentiometer)			
	VOLTAGE ADJ. RANGE Note.5 CURRENT ADJ. RANGE	20.4 ~ 25.2V	30.6 ~ 37.8V	40.8 ~ 50.4V	45.9 ~ 56.7V
		Adjusted for A-type only (via built-in potentiometer)			
OUTPUT		10 ~ 20A	6.6 ~ 13.3A	5 ~ 10A	4.4 ~ 8.9A
	VOLTAGE TOLERANCE Note.3	<u> </u>	±1.0%	±1.0%	±1.0%
	LINE REGULATION	±0.5%	±0.5%	±0.5%	±0.5%
	LOAD REGULATION	±0.5%	±0.5%	±0.5%	±0.5%
		500ms, 80ms 115VAC/230VAC		⊥ 0.3 /0	
	HOLD UP TIME (Typ.)	16ms 115VAC/230VAC			
INPUT	1 ,	90 ~ 305VAC 127 ~ 431VDC			
		47 ~ 63Hz			
	FREQUENCY RANGE	PF≥0.98/115VAC, PF≥0.97/230VAC, PF≥0.95/277VAC at full load			
	POWER FACTOR (Typ.)	94%	95%	94.5%	95%
	EFFICIENCY (Typ.) AC CURRENT (Typ.)	94.5% 95% 95% 95% 95%			
	INRUSH CURRENT(Typ.)	COLD START 35A at 230VAC 2A/211VAC			
	LEAKAGE CURRENT				
PROTECTION	LEARAGE CURRENT	<0.75mA/277VAC			
	OVER CURRENT	105 ~ 125%			
	Constant current limiting, recovers automatically after fault condition is removed				
	SHORT CIRCUIT	Constant current limiting, recovers automatically after fault condition is removed			
	OVER VOLTAGE	27 ~ 33V	40 ~ 50V	53 ~ 63V	60 ~ 70V
		Shut down output voltage, re-power on to recover			
	OVER TEMPERATURE	Shut down output voltage, re-power on to recover			
ENVIRONMENT	WORKING TEMP.	-55 ~ +65°C (Refer to "Derating Curve")			
	WORKING HUMIDITY	20 ~ 95% RH non-condensing			
	STORAGE TEMP., HUMIDITY	-60 ~ +80°C, 10 ~ 95% RH			
	TEMP. COEFFICIENT	±0.02%/°C (0~60°C)			
	VIBRATION	20 ~ 500Hz, 10G 12min./1cycle, period for 72min. each along X, Y, Z axes			
SAFETY & EMC	SAFETY STANDARDS	UL60950-1, IP65 (or IP68 for HEP-480 Blank-Type) approved ; design refer to TUV EN60950-1			
	WITHSTAND VOLTAGE	I/P-O/P:3.75KVAC I/P-FG:2.0KVAC O/P-FG:1.5KVAC			
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH			
	EMC EMISSION	Compliance to EN55022 (CISPR22) Class B, EN61000-3-2,-3			
	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, EN55024, light industry level (surge 6KV), criteria A			
OTHERS	MTBF	89.8K hrs min. MIL-HDBK-217F (25°C)			
	DIMENSION	262*125*43.8mm (L*W*H)			
	PACKING	2.8Kg;4pcs/12.2Kg/0.58CUFT			
NOTE	Ripple & noise are measure Tolerance : includes set up Length of set up time is me Derating may be needed ur The power supply shall be and/or configuration, the fin The ambient temperature d The water protection level to	cially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature. sured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. up tolerance, line regulation and load regulation. measured at cold first start. Turning ON/OFF the power supply may lead to increase of the setup time. d under low input voltages. Please refer to the "STATIC CHARACTERISTICS" for more details. be regarded as one component of the final system. The EMC performance will be affected by the complete system installation ifinal system manufacturers must re-verify overall EMC directive with the complete installation and/or configuration. e derating of 3.5°C/1000m is needed for operating altitude greater than 2000m(6500ft). el test for the IP68 rating is performed 1000mm below the surface of the water for 1 month. anty statement on MEAN WELL's website at http://www.meanwell.com			



■ Block Diagram PFC fosc : 45KHz PWM fosc : 55KHz RECTIFIERS EMI FILTER POWER PFC & FILTER SWITCHING & RECTIFIERS CIRCUIT O.L.P. DETECTION FG O 0.L.P. PWM CIRCUIT PFC CONTROL CONTROL O.V.P. O.T.P.

■ Derating Curve

■ Static Characteristics

