

Description

STAINLESS STEEL TOP PLATE CASTOR, GREY RUBBER 160MM

Fixed

KF5BA160-325L



Part Number

Swivel

KP5BA160-325L




Swivel and brake

KP5BD160-325L



	Fixed	Swivel	Swivel+brake
Wheel Diameter ØD	160 mm		
Overall Height H	197 mm ±1		
Size of plate A X B	129 x 106 mm±1		
Plate hole centres a x b	105 x 80 mm±0,3		
Plate hole	11 mm		
Offset F ±1	\	52 mm	52 mm
Width of Tread	38 mm±0,5		
Hardness of tread	shore A ± 88		
Load capacity	150 Kg		
Weight	1,2 kg	1,7 kg	2,1 kg
Temperature	- 10 / + 50 °C		



Castor Assembly :

Pressed stainless steel -AISI 304-. Swivel on two rows of balls.
 Fastening by top plate.
 Total lock. Metal pedal.

Wheel :

Wheel centre made of Grey Polypropylene.
 Tread : Thermoplastic rubber, grey non marking.
 Hub : Plain bore.

Features :

Low starting effort,
 Bonded Rubber,
 Corrosion resistant, easy to clean
 Suited for Food industry, Hospital or Industrial Kitchen equipment.
 Medium duty.