

# PMT (10X38) GN - Insert label



0831091

<https://www.phoenixcontact.com/gb/products/0831091>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marking label for conveyed fluids, for equipping CARRIER-PMP (110x38), CARRIER/L-PMP (110x38), and CARRIER-PMP-ENCLOSED (110x38) according to DIN 2403



## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 0831091             |
| Packing unit                         | 100 pc              |
| Minimum order quantity               | 100 pc              |
| Sales key                            | BG261Z              |
| Product key                          | BG261Z              |
| Catalog page                         | Page 364 (C-3-2019) |
| GTIN                                 | 4046356941242       |
| Weight per piece (including packing) | 0.642 g             |
| Weight per piece (excluding packing) | 0.642 g             |
| Customs tariff number                | 39199080            |
| Country of origin                    | DE                  |

# PMT (10X38) GN - Insert label



0831091

<https://www.phoenixcontact.com/gb/products/0831091>

## Technical data

### Product properties

|                     |                                                         |
|---------------------|---------------------------------------------------------|
| Product type        | Labeled systems marker                                  |
| Area of application | Identification of flow substances according to DIN 2403 |

### Marking

|                                     |   |
|-------------------------------------|---|
| Number of individual labels         | 1 |
| Number of individual labels per row | 1 |

### Dimensions

|                   |         |
|-------------------|---------|
| Width             | 10 mm   |
| Length            | 38 mm   |
| Material strength | 1.10 mm |

### Material specifications

|            |                                |
|------------|--------------------------------|
| Color      | green (RAL 6021)               |
| Material   | PVC                            |
| Components | Free from silicone and cadmium |

### Environmental and real-life conditions

#### UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |
| Test duration | 96 h                                  |

#### Ambient conditions

|                                                     |                                                                                          |
|-----------------------------------------------------|------------------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | -30 °C ... 80 °C                                                                         |
| Recommended ambient temperature (storage/transport) | 10 °C ... 30 °C                                                                          |
| Recommended humidity (storage/transport)            | 40 % ... 70 % (Storage in a dry and dark place in the original packaging is recommended) |
| Shelf life                                          | 12 months                                                                                |

### Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Mounting

|               |          |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

# PMT (10X38) GN - Insert label



0831091

<https://www.phoenixcontact.com/gb/products/0831091>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27281104 |
| ECLASS-12.0 | 27281104 |
| ECLASS-13.0 | 27281104 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001288 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# PMT (10X38) GN - Insert label



0831091

<https://www.phoenixcontact.com/gb/products/0831091>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)