







RCBO compact 1 MW 1-pole+N 4.5 kA type A 30 mA C6

Model	
product brand name	SENTRON
product designation	RCBO
design of the product	Instantaneous
General technical data	
number of poles	2
number of poles with protection	1
design of pole	1P+N
tripping characteristic class	C
mechanical service life (operating cycles) typical	10 000
overvoltage category	3
degree of pollution	2
Voltage	
type of voltage of the operating voltage	AC
insulation voltage (U <sub>i</sub> ) rated value	253 V
surge voltage resistance rated value	4 000 V
surge current resistance at (8/20) $\mu$ s	1 kA
tripping fault current rated value	30 mA
<ul style="list-style-type: none"> <li>• operational current                             <ul style="list-style-type: none"> <li>— at 30 °C rated value</li> <li>— at 40 °C rated value</li> <li>— at 45 °C rated value</li> <li>— at 50 °C rated value</li> <li>— at 55 °C rated value</li> <li>— at 60 °C rated value</li> <li>— at 65 °C rated value</li> <li>— at 70 °C rated value</li> </ul> </li> <li>• operational current at AC rated value</li> </ul>	<ul style="list-style-type: none"> <li>6 A</li> <li>5.64 A</li> <li>5.46 A</li> <li>5.28 A</li> <li>5.04 A</li> <li>4.86 A</li> <li>4.62 A</li> <li>4.44 A</li> <li>6 A</li> </ul>
residual current type	A
Supply voltage	
supply voltage <ul style="list-style-type: none"> <li>• at AC rated value</li> <li>• for testing equipment minimum</li> </ul>	<ul style="list-style-type: none"> <li>230 V</li> <li>195 V</li> </ul>
operating frequency	50/60 Hz
supply voltage frequency rated value	50 Hz
Protection class	
protection class IP	IP20, if the distribution board is installed, with connected conductors
Breaking Capacity	
switching capacity current <ul style="list-style-type: none"> <li>• according to EN 60898 rated value</li> <li>• according to IEC 60947-2 rated value</li> </ul>	<ul style="list-style-type: none"> <li>4.5 kA</li> <li>5 kA</li> </ul>
short-circuit current breaking capacity (I <sub>cn</sub> ) according to EN 61009-1 rated value	4.5 kA
rated residual switching capacity (I $\Delta$ m) according to IEC 61009-1	4.5 kA
energy limitation class	3
Dissipation	

<b>power loss [W]</b>	
• maximum	1.2 W
<b>Product details</b>	
<b>product feature touch protection</b>	Yes
product component neutral conductor switching	Yes
<b>product feature halogen-free</b>	Yes
<b>product feature silicon-free</b>	Yes
<b>Connections</b>	
<b>connectable conductor cross-section solid</b>	
• minimum	0.75 mm <sup>2</sup>
• maximum	16 mm <sup>2</sup>
<b>connectable conductor cross-section stranded</b>	
• minimum	0.75 mm <sup>2</sup>
• maximum	16 mm <sup>2</sup>
<b>connectable conductor cross-section finely stranded with core end processing</b>	
• minimum	0.75 mm <sup>2</sup>
• maximum	10 mm <sup>2</sup>
<b>tightening torque with screw-type terminals</b>	
• minimum	1.2 N·m
• maximum	2 N·m
<b>position of power supply cord</b>	Either top or bottom
<b>Mechanical Design</b>	
<b>height</b>	90 mm
<b>width</b>	18 mm
<b>depth</b>	77 mm
<b>installation depth</b>	70 mm
<b>number of modular width units</b>	1
<b>mounting position</b>	any
<b>Net Weight</b>	126 g
<b>weight with packaging</b>	133 g
<b>Environmental conditions</b>	
<b>influence of the surrounding temperature</b>	Max. 95% humidity
<b>ambient temperature during operation</b>	
• minimum	-25 °C
• maximum	45 °C
<b>ambient temperature during storage</b>	
• minimum	-40 °C
• maximum	75 °C
<b>number of test cycles for environmental testing according to IEC 60068-2-30</b>	28
<b>Approvals Certificates</b>	
Environmental Product Declaration	
• global warming potential [CO2 eq] / during manufacturing	1.32 kg
• global warming potential [CO2 eq] / during sales	0.0287 kg
• global warming potential [CO2 eq] / during operation	16.6 kg
• global warming potential [CO2 eq] / after end of life	0.00156 kg
• global warming potential [CO2 eq] / total	17.95026 kg
<b>Environment</b>	<b>General Product Approval</b>
  <a href="#">Environmental Confirmations</a>	 
<b>General Product Approval</b>	<b>Test Certificates</b>

[Confirmation](#)



[Special Test Certificate](#)

[Miscellaneous](#)

other

Dangerous goods



[Confirmation](#)

[Miscellaneous](#)

[Miscellaneous](#)

[Transport Information](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SV1313-7KK06>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SV1313-7KK06>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[https://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SV1313-7KK06](https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SV1313-7KK06)

CAX-Online-Generator

<https://www.siemens.com/cax>

Tender specifications

<https://www.siemens.com/specifications>

Characteristic curves

[https://curves.simaris.siemens.com/curves/<mmp\\_prod\\_noCOMP="HAUPT"></mmp\\_prod\\_no>](https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP=)

