

Eaton 171335

Catalog Number: 171335

Eaton Moeller® series SL4 Ba15d continuous light module, yellow



General specifications

Product Name	Catalog Number
Eaton Moeller® series SL4 Continuous light module	171335
	EAN
	4015081678723
Product Length/Depth	Product Height
43 mm	75 mm
Product Width	Product Weight
43 mm	0.037 kg
Certifications	Catalog Notes
UL Category Control No.: NKCR	Without light elements
UL 508	
CSA Class No.: NKCR7	
IEC/EN 60947-5-1	
CE	
UL report applies to both US and Canada	
UL File No.: E29184	
CSA-C22.2 No. 14-10	
Certified by UL for use in Canada	
CSA-C22.2 No. 94-91	
IEC/EN 60529	
UL	

Features & Functions

Color

Yellow

Enclosure color

Black

Functions

Continuous light

Light modules

Filament lamp max. 4 W

Number of modules

Max. 10 (with base for mounting on both sides)

Max. 5 (with standard base)

General

Connection to SmartWire-DT

No

Degree of protection

NEMA 4

IP66

Lifespan, electrical

3,000 h

Light type

Continuous light

Material

Enclosure: Polycarbonate (PC)

Cap: Polycarbonate (PC)

Mounting Method

BA15d lamp socket

Mounting position

As required

Overvoltage category

III

Pollution degree

3

Product Category

SL signal towers

Radiation angle

360 °

Rated impulse withstand voltage (Uimp)

4000 V AC

Shock resistance

Mechanical, According to IEC/EN 60068-2-27

15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms

Type

Continuous light module

Voltage type

AC/DC

Climatic environmental conditions

Ambient operating temperature - min

-30 °C

Ambient operating temperature - max

60 °C

Climatic proofing

Damp heat, constant, to IEC 60068-2-78

Damp heat, cyclic, to IEC 60068-2-30

Electrical rating

Leakage current

0.003 A

Power consumption

Max. 4 W with the specified voltages

Rated insulation voltage (Ui)

250 V

Rated operational voltage (Ue) at AC - min

24 V

Rated operational voltage (Ue) at AC - max

250 V

Rated operational voltage (Ue) at DC - min

24 V

Rated operational voltage (Ue) at DC - max

250 V

Resources

Brochures

[SL4, SL7, SLC Stack light overview brochure BR047017](#)

Catalogs

[eaton-rmq-titan-brochure-br047004en-en-us.pdf](#)

[eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-00004257.pdf](#)

[DA-DC-00004253.pdf](#)

Drawings

[eaton-operating-sl4-continuous-light-dimensions.eps](#)

[eaton-operating-button-sl7-continuous-light-symbol-004.eps](#)

[eaton-operating-sl7-continuous-light-symbol.eps](#)

eCAD model

[ETN.171335.edz](#)

Installation instructions

[IL047005ZU](#)

Installation videos

[Signal towers SL4 and SL7](#)

mCAD model
DA-CD-sl4_bfl4
DA-CS-sl4_bfl4



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia