

GERBEURS



60 to 600 KG

Manual Levfix™

A range of manually-operated stackers designed to ensure ergonomic and safe use for professionals. Functional and modular, they facilitate the daily handling of drums, canisters, reels, totes, cartons, etc. thanks to a range of standard accessories.

Performance :

- Robust construction for intensive use.
- 2 lifting speeds, foot-operated jack.
- Lightweight: unladen weight 90 kg.

Safety :

- Rear wheels with foot protection and brake.
- Device to prevent the stacker from tipping over in the event of an obstacle on the descent path.
- Compliant with Machinery Directive 2006/42/EC and ISO 3691-5.

Maintenance and warranty :

- 10-year guarantee, excluding wearing parts. Components available from stock. After-sales service and maintenance at our Normandy factory.

Accessories :

- **Rotobidon™** : in 304 L stainless steel, empties a can or small cubic barrel 210 to 340 mm wide, 255 to 360 mm deep and 345 to 555 mm high, or a cylindrical barrel Ø 280 to Ø 340 mm, 345 to 555 mm high
- **Manual 2-axis coil turner with jaws**: turns a coil from horizontal to vertical and vice versa. Reel pick-up via mandrel. Pick-up capacities: inside Ø 70 mm, maximum outside Ø 900 mm, width: 200 to 600 mm
- **Stainless steel tray**: dimensions 500 × 400 mm
- **Stainless steel roller spur and stainless steel V-tray**: max. reel Ø 600 mm, max. reel width 600 mm
- **Roller spur**: stainless steel for reels with Ø 53 mm bore. Total length 515 mm, usable length 480 mm
- **Steel sliding forks** :
 - 200 kg model: in 30 × 30 mm square tube, 440 mm long, spacing adjustable from 180 to 430 mm
 - 600 kg model: in 35 × 35 mm square tube, 500 mm long, adjustable spacing from 295 to 755 mm
- **Automatic drum clamp**: for metal or plastic drums, with rim, or for plastic drums with lid from 60 to 220 L.
- **Manual drum turner**: empties a Ø 600 mm metal drum. 360° rotation, controlled by handwheel on irreversible gearbox. Clamping system via metal belt at with hook tensioner and 50 mm wide strap.




840 008 471 - with automatic drum clamp

Video



Longerons

- **Standard**: fitted with bogie rollers, they make it easier to pass under a pallet.
- **Supervisors**: allow you to supervise a pallet.
- **Pallet guides**: used to reach over a pallet to pick up a load (drum, reel, etc.) located at the bottom of the pallet.



Managers



Pallet hanger



Reference	Accessories	CU	Race	Minimum/ maximum lifting height	Lift speed	Height excl.	Longerons	Useful spacing between side rails	Braked front and rear wheels	Weight		
845 008 019	Rotobidon™	60 ⁽¹⁾	1350	10/1470	40 or 70 mm / pumping	1930	Standards	450	Ø 80 / Ø 125 polyamide	108		
855 000 968	Coil turner	80 ⁽¹⁾		175/1575						108		
855 000 967	Stainless steel tray	100 ⁽¹⁾		185/1785						103		
855 000 965	Roller spur with V plate	100 ⁽¹⁾		200/1800						99		
855 000 964	Stainless steel roller spur	200 ⁽¹⁾		180/1780						97		
855 000 966	Sliding forks	200 ⁽¹⁾		80/1530	20 or 35 mm / pumping					Managers	860	104
855 010 530		600 ⁽²⁾		35/1580								153
840 008 471	1-barrel automatic clamp	120- 150 ⁽¹⁾		520/2115	40 or 70 mm / pumping		Pallet hanger	885		860	127	
845 010 475		300 ⁽²⁾		515/2095	20 or 35 mm / pumping						156	
845 008 061		500 ⁽²⁾		880/2185							156	
845 008 018	Drum turner	350 ⁽²⁾		305/1635							Managers	166

⁽¹⁾ Capacity at 250 mm from masts in accordance with ISO 3691-5 standard / ⁽²⁾ Capacity at 500 mm from masts in accordance with ISO 3691-5 standard



845 008 019 - Rotobidon™



855 000 968 - Coil turner




855 000 967 - Stainless steel




855 000 965 - Roller spur + V
plate



855 000 964 - Roller spur



855 000 966 - Sliding forks



840 008 471 - 1-barrel
automatic clamp



845 008 018 - Drum turner

Available in a semi-electric version