




Automotive Parts > Automotive Connectors > Data Connectivity Headers



Connector System: **Wire-to-Board**

Sealable: **No**

Shielded: **No**

PCB Mount Orientation: **Horizontal**

Number of Positions: **1**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Mixed & Hybrid Connector	No
Connector System	Wire-to-Board
Sealable	No

Configuration Features

Number of Rows	1
PCB Mount Orientation	Horizontal
Number of Positions	1

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Connector & Keying Code	B
-------------------------	---

Contact Features

--	--



Outer Contact Plating Material	Tin (Sn)
RF Connector Center Contact Plating Material	Tin (Sn)
Contact Mating Area Plating Material	Gold (Au)
Center Contact	With
Contact Type	Pin
Mating Pin Diameter	.51 mm[.02 in]
Contact Current Rating (Max)	1 A

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

PCB Mount Retention Type	Solder Tail
Connector Mounting Type	Board Mount

Housing Features

Housing Color	Jet Black
---------------	-----------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Operating Frequency Range	0 – 6 GHz
Solder Process	Reflow Solder Capable
Assembly Process Feature	Board Standoff
Shielded	No
Circuit Application	Signal

Industry Standards

Compatible With Agency/Standards Products	DIN 72594-1
UL Flammability Rating	UL 94HB

Packaging Features

Packaging Method	Reel
------------------	------

Other

Dielectric Material	PCT GF
---------------------	--------

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Pin-in-Paste capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2474535-1
ADAPTER, SMA F TO FAKRA F W H, STR, 6GHZ



TE Part # 2474533-1
ADAPTER, SMA F TO FAKRA F, NO HOUSING, 6GHZ

Also in the Series | **FAKRA**



Automotive Connector EMC Shielding
(3)



Automotive Connector Locks & Position Assurance(11)



Automotive Housings(7)




Automotive Seals & Cavity Plugs(2)




Automotive Signal & Power Connector Housings(5)




Connector Adapters & Connector Savers(6)



Data Connectivity Headers(394)



Infotainment & Multimedia Cable Assemblies(31)



Other Automotive Connector Accessories(32)

Customers Also Bought



TE Part #826470-3
2X3P MOD II SHROUDED HEADER, RT ANG.



TE Part #826470-4
2X4P MOD II SHROUDED HEADER, RT ANG.



TE Part #2291362-1
4POS,PIN DIA 0.6,HEADER ASSY, CODE A



TE Part #2291392-7
MALE ASM, 1 POS, R/A, PCB, FAKRA



TE Part #2315834-1
6POS,HSD DIA 0.6,HDR ASSY,90DEG, COD A



TE Part #2317515-1
2X10POS,NANOMQS,HDR ASSY, 90DEG,SMD,COD A



TE Part #1-2317779-3
24POS,HYBRID,HDR ASSY,90DEG, SLDR



TE Part #2326784-1
32POS,TAB0.64X0.64,HDR ASSY, 90DEG,SLDR



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2291392-1_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2291392-1_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2291392-1_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English