C1005B-Series THERMAL CIRCUIT PROTECTORS

The C1005B-Series offers the functionality of a switch and circuit breaker in a single compact package, which fits an industry standard .500 x 1.125 mounting hole. This combo device eliminates the need for both a switch and thermal circuit protector on customer panels. By using only this multipurpose product, wiring and assembly costs are greatly reduced, while at the same time, valuable panel real estate is saved. The C1005B-Series is available lighted or unlighted, in a variety of colors, with solder lug or .250 Tabs. Current ratings range from 7-16 amps@125 and 250 VAC and up to 32 VDC.



Household and Commercial Appliances Transportation

Marine

Telecommunications

Power Strips

Audio-visual Equipment

Medical equipment

Power supplies

Generators

Safety Regulatory Agency Approvals:

UL, CUL, TUV





A SWITCH & CIRCUIT PROTECTOR IN ONE SMALL, COMPACT PACKAGE!

Product Highlights:

- Industry Standard .550 X 1.125 mounting hole (14mm X 28.6mm)
- Ratings from 7-16 Amps
- Standard Reset/Off Legend
- Aesthetically pleasing Curved Rocker & Angular Bezel
- .250 Tabs or Solder Lug Terminations
- 65°C Max Operating Temperature
- 1000 AIC Interrupting Capacity
- 1500 VAC Dielectric Strength
- 100 megohms at 500 VDC Insulation Resistance
- Compact Space-saving Envelope
- UL1077, UL1363, IEC 60934



1 SERIES C1005B

2 ILLUMINATION

Non-Lighted Lighted

3 TERMINATION

Solder Lug В .250 Tab

4 CURRENTRATING (AMPERES)

| 07 | 7 amps | 12 | 2 1 | 2 amps |
|----|---------|----|-----|--------|
| 80 | 8 amps | 13 | 3 1 | 3 amps |
| 09 | 9 amps | 14 | 1 | 4 amps |
| 10 | 10 amps | 15 | 5 1 | 5 amps |
| 11 | 11 amps | 16 | 1 | 6 amps |
| | | | | |

Notes:
1 Silver cad oxide switch and breaker contacts are available as a special order. Specify 3 for selection 5

5 CONTACT MATERIAL¹

- SilverCad Oxide (switch), Silver plated copper (breaker)
- SilverCad Oxide (switch & breaker)

6 BEZEL LEGEND IMPRINT

- Black Bezel with white legend
- White Bezel with black legend
- Gray Bezel with black legend

7 ROCKER COLOR

- Red Green
- Blue Clear

Note: RESET OFF Legend is standard.

8 LAMP VOLTAGE

- Neon Lamp 125/250 VAC
- Non-lighted


Time Delay

| OVERLOAD | TRIP TIME |
|----------|----------------|
| 100% | NO TRIP |
| 150% | TRIP IN 1 HR. |
| 200% | 5 - 35 SEC. |
| 300% | 1 - 10 SEC. |
| 400% | .45 - 5.5 SEC. |
| 600% | .1 - 20 SEC. |

| CORRECTION FACTOR ¹ | | | |
|--------------------------------|--------|--|--|
| 0°C | x .67 | | |
| 10°C | x .72 | | |
| 15°C | x .83 | | |
| 18°C | x .87 | | |
| 25°C | x 1.00 | | |
| 32°C | x 1.05 | | |
| 40°C | x 1.18 | | |
| 50°C | x 1.33 | | |
| 60°C | x 1.67 | | |

1 To adjust the breaker ratings for ambient temperature multiply the breaker rating by the factor. (ex: 5 amp rating at 0°C: 5 x .67 = 3.3 amp. Select 3 amp rating.) 2500 amps @ 32 VDC only. AIC rating is 1000 amps for AC applications.

Dimensional Specifications: in. [mm]



*Manufacturer reserves the right to change product specification without prior notice.