



Connectors > Circular Connectors > Standard Circular Connectors



Number of Positions: 8
Connector System: Wire-to-Board
Shell Plating Material: Electroless Nickel
Circular Connector Shell Size: 3.5
Contacts Preloaded: Yes

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Circular Connector Type	Receptacle

Configuration Features

Number of Positions	8
Contacts Preloaded	Yes

Signal Characteristics

Data Rate	10 Gb/s
-----------	---------

Body Features

Shell Plating Material	Electroless Nickel
------------------------	--------------------

Housing Features


Circular Connector Shell Size	3.5
-------------------------------	-----

Packaging Features

Packaging Quantity	1
--------------------	---

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)






EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | CeeLok FAS-T Connector



Standard Circular Connectors(30)

Also in the Series | CeeLok FAS-T Nano Connector



Standard Circular Connectors(30)



Customers Also Bought

TE Part #1410946-2
MULTI-GIG SOC. CAP SCREW,
CUSTOMIZED HDW

TE Part #CONSMB002-G
SMB Jack 50 Ohm PCB Through Hole

TE Part #CONSMA002-G
SMA Jack 50 Ohm PCB Through Hole

TE Part #1-2176338-5
CRGCQ 0402 220R 5%

TE Part #5229912-1
KIT, PLUG, 50 POS,B SLOT C/LOK

TE Part #1-1469492-1
MULTIGIG RT 9MM GUIDE/ESD 0 DEG

TE Part #6-6609959-6
PM0S0DBX0=C5280

TE Part #CONSMA002-SMD-G-T
SMA Jack 50 Ohm PCB Surface Mount

TE Part #CSE-SMBM-152-SMBM
SMB to SMB 152mm RG316

TE Part #1925251-1
TCM008PC1TT036 = Circular

Documents

Product Drawings

QCM008M5P = Circular

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1925261-1_A_c-1925261-1-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1925261-1_A_c-1925261-1-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1925261-1_A_c-1925261-1-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Product Specifications

Product Specification

English