




SECT. "A" - "A

△ MATERIAL:
HOUSING: L.C.P (HIGH TEMP THERMO PLASTIC)
UL 94V-0, NATURAL.
CONTACT: BRASS.

△ 2 FINISH:
CONTACT AREA: 0.0002 MIN GOLD ON
0.0013 MIN ALL OVER NICKEL.
SOLDERING AREA: 0.002 MIN MATTE-TIN.

3. POSITION SERIES: SEE TABLE.


4. CONN STACK HEIGHT COMBINE OF PLUG "Y" H VS REC "X" H.
STACK HEIGHT = Y + X - 5

5 OBSOLETE PARTS: OBSOLETE CIS STREAMING PER
D.RENAUD/D.SINISI.

△ 6 DATE CODE MARKING

P/N SEE SHEET 2 OF 2.



DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.30 2 PLC ±0.25 3 PLC ±0.20 4 PLC ± ANGLES ±3°		DWN 30AUG04 FLORENCE TAN CHK ERIC TNG APVD SF LFONG PRODUCT SPEC 108-5390 APPLICATION SPEC 114-5254 WEIGHT -		 TE Connectivity	
		NAME PLUG ASSEMBLY 6H TYPE (0.5 and 0.8 BOSS LENGTH) FOR FH 0.8mm PITCH B-T-B CONNECTOR		SIZE A3 CAGE CODE 00779 DRAWING NO C-5179029		SCALE 4:1 SHEET 1 OF 2 REV B1	
MATERIAL 		FINISH 		CUSTOMER DRAWING			


4

3


2

1


LOC	DIST	REVISIONS				
DY	-	P	LTR	DESCRIPTION	DATE	APVD
		-		SEE SHEET 1 OF 2	-	-




SECT A-A



SECT B-B



REFERENCE PICTURE OF TUBE PACK



DETAIL "B"
(SCALE 5-1)

5	12	0.8	36.2	37.8	31.2	80	3	3
5	16	0.8	28.2	29.8	23.2	60	3	2
5	22	0.8	20.2	21.8	15.2	40	3	1
	5	0.5	84.2	85.8	79.2	200	1-	-0
	6		76.2	77.8	71.2	180		-9
	6		68.2	69.8	63.2	160		-8
	7		60.2	61.8	55.2	140		-6
	9		52.2	53.8	47.2	120		-5
	10		44.2	45.8	39.2	100		-4
	12		36.2	37.8	31.2	80		-3
	16		28.2	29.8	23.2	60		-2
	22	0.5	20.2	21.8	15.2	40		5179029-1
QTY/ TUBE	D	C	B	A	POS.	CONN	P/N	

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.30 2 PLC ±0.25 3 PLC ±0.20 4 PLC ±- ANGLES ±3°		DWN 30AUG04 FLORENCE TAN CHK ERIC TNG APVD SEI FONG PRODUCT SPEC 108-5390 APPLICATION SPEC 114-5254 WEIGHT -		STE TE Connectivity		
MATERIAL		FINISH		CUSTOMER DRAWING		NAME PLUG ASSEMBLY 6H TYPE (0.5 and 0.8 BOSS LENGTH) FOR FH 0.8mm PITCH B-T-B CONNECTOR		
						SIZE A3	CAGE CODE 00779	DRAWING NO C-5179029
						SCALE -		SHEET 2 OF 2
								REV B1