

Eaton 135733

Catalog Number: 135733

Eaton Moeller® series E65 Thru-beam photoelectric sensor, receiver, Sn=15m, 4L, 10-30VDC, light, NPN, PNP, quad 40, insulated material E65-SMTD15-HLD

General specifications



| Product Name | Catalog Number |
|--|----------------|
| Eaton Moeller® series E65 Thru-beam photoelectric sensor | 135733 |
| | EAN |
| | 4015081325269 |
| Product Length/Depth | Product Height |
| 139.7 mm | 139.7 mm |
| Product Width | Product Weight |
| 38.1 mm | 0.11 kg |
| Certifications | Catalog Notes |
| Certified by UL for use in Canada | Yellow |
| UL | |
| CE | |
| CSA File No.: UL report applies to both | |
| US and Canada | |
| UL 508 | |
| UL File No.: E166051 | |
| CSA-C22.2 No. 14 | |
| IEC/EN 60947-5-2 | |
| UL Category Control No.: NRKH, NRKH7 | |

Product specifications

Type

Optical sensors

Device type

Receiver

Electric connection type

Plug-in connection

Fitted with:

Transmitter (for combination with detector)

Enclosure material

Plastic

Enclosure type

Cuboid

Operating mode

Switching principle: Light switching

Explosion safety category for dust

None

Explosion safety category for gas

None

Functions

Protection against polarity reversal

Protection against wire breakage

Thru-light beam

For combination with transmitter

Short-circuit protection

Voltage type

DC

Wire size

0

Connection type

Plug-in connection M12 x 1

4-wire

Cable sheath material

Polyvinyl chloride (PVC)

Light type

Polarity free red light

Degree of protection

Resources

Catalogs

Product Range Catalog Sensors – products, basic information, applications

Declarations of conformity

DA-DC-00004652.pdf

DA-DC-00004657.pdf

Drawings

eaton-proximity-switches-dimensions-012.eps

eaton-proximity-switches-e65-diffuse-reflective-sensor-dimensions.eps

eaton-proximity-switches-e65-3d-drawing.eps

Installation instructions

IL05305004Z

mCAD model

DA-CS-90_28290_012

DA-CD-90_28290_012

NEMA 6

IP68

Interface type

Other

LED indicator

Status indication of Operating voltage: Green LED

Status indication of Switching state: Red LED

Switch function type

Other

Load current

Max. 100 mA (I_e)

Laser protection class

None

Operation agent-safety class

Safety class 2

Shock resistance

50 g, Mechanical, Shock duration 10 ms

Optical surface material

Plastic

Output current (mA) - max

100 mA

Output current at protected output - max

0 mA

Rated control supply voltage (U_s) at AC, 50 Hz - max

0 V

Rated control supply voltage (U_s) at AC, 50 Hz - min

0 V

Rated control supply voltage (U_s) at AC, 60 Hz - max

0 V

Rated control supply voltage (U_s) at AC, 60 Hz - min

0 V

Rated control supply voltage (U_s) at DC - max

30 V

Rated control supply voltage (U_s) at DC - min

10 V

Rated switching distance (S_n)

15000 mm

Reflector distance - min

0 mm

Sensor height

55 mm

Sensor length

41 mm

Switching distance - max

15000 mm

Switching voltage of OSSD at state high

30 V

Transmission range of the safety field

0 m

Voltage rating - max

30 V

Safety type (IEC 61496-1)

1

Switching frequency

500 Hz

Sensing mode

Light switching

Switching output type

NPN

Sensor material

Insulated material

Wavelength of the sensor

660 nm

Width sensor

33 mm

Product category

E65 SM Series

Response time

1 ms

Ambient operating temperature - max

55 °C

Ambient operating temperature - min

-25 °C

Ambient storage temperature - max

70 °C

Ambient storage temperature - min

-25 °C

Diameter sensor

0 mm

Light dot size

0 mm²

Number of contact energized outputs with signalling function

0

Number of outputs (protected contact energized)

0

Number of outputs (protected semiconductor)

0

Number of outputs (semiconductor with signaling function)

2

Opening angle

0 °

Operating temperature - max

55 °C

Operating temperature - min

-25 °C

Operational current (Ib) in the switched state at 24 V DC

20 A

Adjustment type

Other