






THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
COPYRIGHT ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
J	-	A5		REVISED PER ECO-11-005030	26APR11	RK HMR




1. 材料:ハウジング:ガラス入り熱可塑性ポリエステル樹脂(94V-0)、色:黒
コンタクト:銅合金
リテンションレグ:錫めっき済銅合金

- 2. めっき:全面:ニッケル下地めっき1.27μm以上
- 3. めっき:接触部 2 の上に金めっき0.38μm以上
- 4. めっき:コンタクト半田付部: 2 の上に錫めっき2μm以上
- 5. 文字の形状、大きさ、および位置については、大略を示すものであり、詳細を示すものではありません。
- 6. Y KEY形状は、X KEY形状と左右対称





1. MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC POLYESTER(94V-0), COLOR: BLACK
CONTACT: COPPER ALLOY
RETENTION LEG: PRE-TIN COPPER ALLOY

- 2. FINISH(ALL OVER): NICKEL PL. 1.27μmMIN
- 3. FINISH(CONTACT AREA): GOLD PL. 0.38μmMIN AFTER 2
- 4. FINISH(CONTACT TAIL): TIN PL. 2μmMIN AFTER 2
- 5. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.
- 6. THE KEYING ARRANGEMENT OF "Y" IS SYMMETRIC WITH "X".



推奨基板取付穴寸法: コネクタ搭載面(非累積公差)
PC基板厚: 1.0~1.6±0.1
RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1

20	Y	9	22.5	26.0	27.6	2-1827875-0
20	X	9	22.5	26.0	27.6	1-1827875-0
16	Y	7	17.5	21.0	22.6	2-1827875-8
16	X	7	17.5	21.0	22.6	1-1827875-8
12	Y	5	12.5	16.0	17.6	2-1827875-6
12	X	5	12.5	16.0	17.6	1-1827875-6
10	Y	4	10.0	13.5	15.1	2-1827875-5
10	X	4	10.0	13.5	15.1	1-1827875-5
8	Y	3	7.5	11.0	12.6	2-1827875-4
8	X	3	7.5	11.0	12.6	1-1827875-4
6	Y	2	5.0	8.5	10.1	2-1827875-3
6	X	2	5.0	8.5	10.1	1-1827875-3
4	Y	1	2.5	6.0	7.6	2-1827875-2
4	X	1	2.5	6.0	7.6	1-1827875-2
POS	KEY	n	A	B	C	PART NO

DIMENSIONS: 単位: 耗 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3, ±5° 0-PLC ± 1-PLC ±0.5 2-PLC ±0.13 3-PLC ±0.013 4-PLC ±0.0001 ANGLES ± MATERIAL 材料		DWN T.KUDO 14JAN2005		 TE Connectivity	
				CHK D.MITSUGI 14JAN2005			
				APVD D.MITSUGI 14JAN2005		NAME 名称 DYNAMIC D1200D 2.5mmPITCH HDR ASSY (V-TYPE) 4-20POS	
				PRODUCT SPEC 製品規格 108-78268			
				APPLICATION SPEC 取付適用規格 114-5377			
				WEIGHT -			
CUSTOMER DRAWING		SCALE 尺度 4:1		SHEET 1 OF 3		REV A5	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT —

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

L T R



DESCRIPTION

DATE _____

DWN

APVD

SEE SHEET 1



推奨基板取付穴寸法：コネクタ搭載面（非累積公差）











PC基板厚: 1.0~1.6±0.1

RECOMMEND PC BOARD HOLE PATTERN

: CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)

PC BOARD THICKNESS : 1.0~1.6±0.1

ONLY 4POS



4POS(X-KEY): 1-1827875-2

6POS(X-KEY): 1-1827875-3

8POS(X-KEY): 1-1827875-4

DIMENSIONS: 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		DWN T. KUDO 14JAN2005		 TE Connectivity							
				CHK D. MITSUGI 14JAN2005									
MATERIAL		FINISH		APVD D. MITSUGI 14JAN2005		NAME DYNAMIC DI200D 2.5mmPITCH HDR ASSY (V-TYPE) 4-20POS							
				PRODUCT SPEC 108-78268									
				APPLICATION SPEC 114-5377		SIZE A3		CAGE CODE 00779		DRAWING NO C-1827875		RESTRICTED TO -	
				WEIGHT -		CUSTOMER DRAWING		SCALE 4.1		SHEET 2 OF 3		REV A5	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT —

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR










DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1



10POS(X-KEY):1-1827875-5

12POS(X-KEY):1-1827875-6

16POS(X-KEY):1-1827875-8

DIMENSIONS:

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0.000
1.000
2.000
3.000
4.000
ANGLES
FINISH

MATERIAL

DWN T.KUDO 14JAN2005

CHK D.MITSUGI 14JAN2005

APVD D.MITSUGI 14JAN2005

PRODUCT SPEC

108-78268

APPLICATION SPEC

114-5377

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME

DYNAMIC D1200D 2.5mmPITCH
HDR ASSY (V-TYPE)
4-20POS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1827875

SCALE

4:1

SHEET

3

OF

3

REV

A5