

CANAL ELECTRONIC CO LTD  
 MR C J CHEN  
 5TH FL  
 10 LANE 218 CHUNG HSING RD, SEC 2  
 SHINTEN CITY  
 TAIPEI TAIWAN

**RE: Project Number(s) - 03CA27669**

Your most recent Certification is shown below. You may also view this information, or a portion of this information (depending on the product category), on UL's Online Certifications Directory at [www.ul.com/database](http://www.ul.com/database). Please review the text and contact the Conformity Assessment Services staff member who handled your project if revisions are required. For instructions on placing an order for this information in a 3 x 5-inch format, you may refer to the enclosed order form for UL Card Service.

**WOYR2**  
**Switches, Special Use - Component**

September 25, 2003

**CANAL ELECTRONIC CO LTD**  
**5TH FL 10 LANE 218 CHUNG HSING RD, SEC 2 SHINTEN CITY,**  
**TAIPEI TAIWAN**

**E81103**

Cat. No.	Amps	V	Frequency	HP
A f/b 1 or 2, f/b 1 thru 5, f/b 0 thru 6, fb L, R or T, f/b 01, 21 or 31	5 2	125/250 to GND	60	—
B fb 1 or 2, may be fb 1, 2 or 6, f/b 0 thru 5, fb R or C, fb 1 thru 4, may be f/b L or N, f/b A, C, S, B, R or W, f/b A, C, O, W, S, B, G, R, Y or D, may be f/b 0, 1 or 2, f/b B or N, f/b M, N or S	10/15	250/125	60	—
CS-20-5220	1 6/3	125 "L" 125/250	60 60	— —
CS-20-5220A	3/1.5 3	125/250 125 "L"	60 60	— —
CS-30-7928, CS-30-7928T CS-30-7800	1.5 6/3	125 "L" 125/250	60 60	— —
F Series	15/10	125/250	60	—
M140-T01	5/3	125/250	60	—
M141-T02A, M141-T02B M141-T02C	10	125/250	60	—
PS-1	15/10	125/250	60	—
PS-2, may be f/b B1,	15/10	125/250	60	—



Cat. No.	Amps	V	Frequency	HP
B, W, G or C, f/b P, M, O or H, f/b 4 or 6, f/b T0, T1, T2, T3, T4 or T5, f/b A or B	TV-5	120	60	—
PS-17	1	250	60	—
PS-17-1	3/1	125/250 "1."	60	—
PS17-2				
PS17-3				
PSD-1 may be f/b 2 or 4,	5/7.5	125/250	60	—
may be f/b TV5	—	TV-5	60	—
PSD-1 may be f/b 2 or 4,	8	TV-8 250	60 60	— —
may be f/b TV8				
PB-3 may be f/b 2 or 4, may be f/b T, L or P	8	125/250 TV-8	60	—
R Series	16	125/250	60	1/4
	6.9	250	60	3/4
	20	125	60	
RH Series	16	125/250	60	1/4
	6.9	250	60	3/4
	20	125	60	
RS f/b 01 or 02, w/o suffix letter A	6/3	125/250	60	—
	1	125 T		
SL 13A-012	4/2	125/250	60	—
SL 13A-022				
SL 13B-012	6/3	125/250	60	—
SL 13B-022				
SL 13B-112A	6/3	125/250	60	—
SL 13-112B		or		
SL 13-112C	1	125	DC	—
SL 13-113A	6/3	125/250	60	—
SL 13-113B		or		
SL 13-113C	1	125	DC	—
SL 13-112A1	8.5	125	60	—
SL 13-112B1	8.5	125	60	—
SL 13-112C1	8.5	125	60	—
SL 13-113A1	8.5	125	60	—
SL 13-113B1	8.5	125	60	—
SL 13-113C1	8.5	125	60	—
SL 13-112A2	10/5	125/250	60	—
SL 13-112B2	10/5	125/250	60	—
SL 13-112C2	10/5	125/250	60	—
SL 13-113A2	10/5	125/250	60	—
SL 13-113B2	10/5	125/250	60	—
SL 13-113C2	10/5	125/250	60	—
SL 13-V	6/3	125/250	60	—
SL 14 may be f/b 1 or 2, may be f/b 1 or 2, may be f/b A, B or C, w/wo additional numbers or letters	12 4	125/250 300	60 60	— —
SL 14-23CJ	12	125/250	60	—
SL 15 may be f/b	12	125/250	60	—

Cat. No.	Amps	V	Frequency	HP
1/1 or 2/A or S/H, M, J, or S/A, B, C or S				
SL 16	4A	125	60	—
	2A	250	60	—
SL 18, f/b 1, 2 or 3, f/b 1, 2 or 3, A, B or S, f/b M, H, J or K, f/b additional numbers or letters.	10	125/250	60	—
SL 22, f/b 1 or 2, f/b 1,2 or 3, f/b A or S, f/b H, M or S, f/b (0, 1, 2 or S	3/6	250/125	60	—
MR -2	10	125	60	—
	6	250	60	—
	6	125	60	—
	3	250	60	—
DA f/b 1 or 2 f/b 1, 2, 3, 4 or 5, f/b 0, 1, 2, 3, or 4, f/b T, with additional numbers and letters.	5/3	125/250	60	—
PS-2	16/10	125/250	60	—
MR f/b suffixes	10/8	125/250	60	1/4
SL 15 may be f/b 1, may be f/b 1 or 2 may be f/b (A or S) may be f/b (H, M, or S) may be f/b (A, B, C or S)	12 A	125/250 V ac	60	—
HB Series	20/16	125/250	60	—
HB Series	6	120VL	60	—
HB Series	—	250	60	3/4
TA	6	125	60	—
	3	250	60	—
	3	125VL	60	—
MR-4	12A	125/250VAC	60	—
MR f/b 1, 2 or H, f/b 1, fb, 0, 1 or 2, f/b C or R, f/b 1, 2, 3, 4, 5 or 6, f/b L or N, f/b B, W or A, f/b B, C, O, R, W or A	10	125 V	60	1/4
	8	250 V	60	1/4
	6	250 V	60	—
	6	125 V	60	—
	3	250 V	60	—
PS-5 Series	16	125/250 VAC	60	—
MR5-110-F f/b 1, 2, 3, 4, 5, or 6; f/b A, B, or W; f/b A, B, C, G, O, P, R, U, W or Y; f/b B, W or N; f/b C	6/3	125/250 VAC	60	—
MR-2-1 f/b 1 or 2, f/b 0, 1 or 2, f/b C, f/b 1, 2, 3, 4, 5 or 6, f/b -A, -B or -W f/b A, B, C, G, O, P, R, U, W or Y, f/b 6, 7	20A	125V ac	60	—
	12A	250V ac	60	—
	12A	125V ac	60	—
	10A	250V ac	60	—
CS50-C	6 A	125 Vac	60	—
	3A	250 Vac	60	—
	3A	125 Vac	60	—

Marking: Company name or trademark **CEC**, electrical rating and Recognition Mark on switch or smallest container. If marked on the switch, the catalog number may be provided on the smallest unit container.

---

**See General Information Preceding These Recognitions**

For use only in equipment where the acceptability of the combination is determined by Underwriters Laboratories Inc.