


Product datasheet

Specifications



Self-adhesive base, Thorsman installation material, 4.8mm tie width maximum , clear

IMT46451

 **Launching in:** 15 September 2023

 **Coming soon**

Main

product range	Thorsman installation material
product type	Self-adhesive base
colour	Clear
quantity per package	100 pieces

Complementary

Product destination	For 4.8 mm tie width maximum
Condition of use	Indoor
Fixing mode	Adhesive
Material	PA (polyamide) 6.6
Height	28.0 mm
Width	28.0 mm
Depth	6.4 mm

Environment

Environmental characteristic	Fire resistance 30 s conforming to EN 62275
Flame retardance	Self-extinguishing
Ambient air temperature for operation	-30...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	12.000 cm
Package 1 Length	20.000 cm
Package 1 Weight	182.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	30
Package 2 Height	15.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	6.249 kg
Unit Type of Package 3	P12
Number of Units in Package 3	720
Package 3 Height	105.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	161.500 kg

Contractual warranty

Warranty	18 mois
----------	---------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration

Use Again

Repack and remanufacture	
Take-back	No