




OF-MCL-16-SS

Ruland OF-MCL-16-SS, 16mm Shaft Collar With OD Flats And Holes, 303 Stainless Steel, One-Piece Clamp Style, 34mm OD, 13mm Width



**Additional hardware NOT included*

Description

Ruland OF-MCL-16-SS is a one-piece shaft collar with 16mm bore, 34mm OD, and 13mm width. OF-MCL-16-SS has OD flats and tapped holes for mounting shaft collars to each other or adjacent components. The clamp style design does not mar the shaft, is easy to remove, and is indefinitely adjustable. OF-MCL-16-SS is commonly used for guiding, spacing, stopping, mounting, and component alignment. Equipment manufacturers benefit from the tightly controlled face to bore perpendicularity (TIR of $\leq .05\text{mm}$). Perpendicularity is critical for alignment when the shaft collar is used as a load bearing face, mechanical stop, or for mounting components such as gears or bearings. Proprietary processes have been developed by Ruland to maintain superior fit, finish, and holding power. OF-MCL-16-SS is stamped with the Ruland name and bore size for ease of identification. Forged screws test beyond DIN 912 12.9 standards to ensure maximum holding power. OF-MCL-16-SS is machined from solid bar stock to a fine burr free finish and sourced exclusively from North American mills. Ruland uses 303 stainless steel with hardware of like material for consistent corrosion resistance. Stainless steel hardware undergoes a proprietary surface treatment process to prevent galling. It is RoHS2 and REACH compliant and manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

Product Specifications

Bore B	16 mm	Bore Tolerance	+0.050 mm / +.012 mm
Outer Diameter OD	34 mm	Clearance Diameter C MAX	39.3 mm
Width W	13 mm	Width Tolerance	+0.076 mm / -.254 mm
Threaded Mounting Hole	M5	Distance Across Flats	30 mm
Forged Clamp Screw	M5x16	Screw Material	18-8 300 Series Stainless Steel
Hex Wrench Size	4.0 mm	Screw Finish	Bright
Seating Torque	5.4 Nm	Screw Location R	12.50 mm
Number of Screws	1 ea	Material Specification	Type 303 Austenitic, Non-Magnetic Bar
Temperature	-40°F to 350°F -40°C to 176°C	Finish Specification	Bright
Country of Origin	USA	Weight (lbs.)	0.1600
Note 1	Additional mounting hardware not included.		