



<b>DATA SHEET</b>	0034302
<b>UNITRONIC® LiYCY</b>	valid from : 04.09.2006

## Application

UNITRONIC® LiYCY is a flexible, screened cable for fixed installation and flexible use, but not for high flexible applications in power chains and permanently moved machines. The screen is a protection against electrical interference.

UNITRONIC® LiYCY cables are for use in dry, damp and wet rooms, but not outside.

Design and electrical characteristics acc. to VDE 0812.

## Design

Conductor	fine-wire strands of bare copper wire; 0.14 mm <sup>2</sup> to 1.5 mm <sup>2</sup> , 7-wired for 0.34 mm <sup>2</sup>
Insulation	PVC compound YI2 in acc. with VDE 0207 part 4
Coding	to DIN 47100
Stranding	cores twisted in layers, wrapping by plastic foil
Screening	braid of tinned copper, coverage approx. 85 %
Sheath	PVC compound TM2 in acc. to VDE 0207 part 5, grey

Marking on the sheath

LAPPKABEL STUTTGART **UNITRONIC® LiYCY** Part No. . . . .

## Technical Data

Loop resistance	0.14 mm <sup>2</sup>	max. Ω/km	148
	0.25 mm <sup>2</sup>	max. Ω/km	79.9
	0.34 mm <sup>2</sup>	max. Ω/km	57.5
	0.5 mm <sup>2</sup>	max. Ω/km	38.9
	0.75 mm <sup>2</sup>	max. Ω/km	26
	1.0 mm <sup>2</sup>	max. Ω/km	19.5
	1.5 mm <sup>2</sup>	max. Ω/km	13.3
Specific insulation resistance		min. GΩxcm	10
Mutual capacitance	core/core	nF/km	ca. 120
	core/screen	nF/km	ca. 160
Inductivity		mH/km	ca. 0.65
Operating Voltage (not for power purposes)		V	250
Test voltage		U <sub>eff.</sub> V	1200
Temperature range	static	°C	- 40 to + 80
Minimum bending radius	static		6 x Ø cable
	moved		15 x Ø cable
Flame propagation	flame retardant to VDE 0482, part 265-2-1 / IEC 60332-1		

elaborated by: TE-K: : M. Herb	Document: DB0034302_2EN	page 1 of 1
-----------------------------------	-------------------------	-------------