



### Main

Range	Acti 9
Product name	Acti 9 Isobar B
Product or component type	Distribution board
Device application	Distribution
Enclosure type	Standard
Door type	Overall
Provided equipment	Door Enclosure Earth terminal block Neutral terminal block Earth stud Removable gland plates Blanking plate Front cover Pan assembly
Colour	Cream (RAL 9001)

### Complementary

Enclosure mounting	Surface
Poles description	3P + N
[Ie] rated operational current	250 A at 400/415 V AC 250 A at 220/240 V AC
Breaking capacity	25 kA
Overvoltage category	IV
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Incomer device	Switch disconnecter - 3P + N Switch disconnecter - 4P MCCB - 4P Terminal block - 4P RCCB - 4P
Protection device type	Miniature circuit breaker (MCB) as outgoer Residual current circuit breaker with overcurrent protection (RCBO) as outgoer
Number of ways	6 way(s) (3P) outgoer
Enclosure material	Steel

Surface treatment	Epoxy
Surface finish	Powder paint
Height	484 mm
Width	470 mm
Depth	138 mm
Product weight	10.5 kg

## Environment

Standards	BS EN 61439-3
IP degree of protection	IP3x external conforming to BS EN 60529 IP20 internal conforming to BS EN 60529
IK degree of protection	IK05
Pollution degree	3
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...80 °C