

Pushbutton, 9.1 mm, 1NO+1NC, momentary contact function, 1 NC + 1 NO, bezel white



fields of application

- Mechanical and system engineering
- Model construction
- Home technology

special features

Drucktaster opak, nicht beleuchtbar
 Einbaudurchmesser 9,1, mm
 max. 24 V / 100 mA
 Lötanschluss
 Befestigungstechnik mit Gewinding
 Schutzart IP 40 frontseitig



description

Pushbutton with mounting hole diameter 9.1 mm

Pushbutton with mounting hole diameter 9.1 mm, 1 NC + 1 NO

technical data

➤ general

Bezel color	white
Property of bezel / mushroom	opaque
Collar shape	round
Operating temperature, min.	-25 °C
Operating temperature, max.	70 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	80 °C
illuminated	No
Soldering time for manual soldering, max.	3 sec
Soldering temperature for manual soldering	350 °C
Soldering	Manual soldering
Packaging	Box
Packaging unit	10 pcs.
net weight	2.2 g
Operating life	200,000 cycles
B10	260,000 cycles
Degree of protection, front side, according to DIN EN 60529	IP40
MOQ order	50 pcs.
RoHS compliant	Yes
REACH compliant	Yes

direct links

- RAFI eCatalog

➤ mounting diameters

Outside dimension, length	11 mm
Outside dimension, width	11 mm
Outside dimension, height	32 mm
Mounting hole	9.1 mm
Mounting depth	25 mm
Installation height	7 mm

> mechanical data

Actuation function	momentary contact function
Operating force, max.	5 N
Operating force, min.	5 N
Operating travel, max.	1.5 mm
Contact function	1 NC + 1 NO
Contact system	Bridge contact
Contact material	Gold
Fixing	Threaded ring
Solderability	Yes
Terminal on the rear	Solder terminal

> electrical data

Rated voltage, max.	24 V
Rated current, max.	0.5 A