

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Product name: RENOCLEAN MVE 6006

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses: Cleaner/degreaser

Uses advised against: No uses advised against identified.

1.3 Details of the supplier of the safety data sheet

Manufacturer / Supplier FUCHS LUBRICANTS (UK) PLC.
New Century Street
ST1 5HU Hanley
Telephone: +44 (0) 1782 203700

Contact Person: Product Safety department
E-mail: product.safety@fuchs.com
Telephone: +44 (0) 1782 203700

1.4 Emergency telephone number: UK NHS: Dial 111

SECTION 2: Hazards identification

Product name: RENOCLEAN MVE 6006

2.1 Classification of the substance or mixture

The product has been classified and labelled as hazardous according to regulation GB-CLP.

Classification according to GB-CLP.

Physical Hazards

Aerosol	Category 1	H222: Extremely flammable aerosol. H229: Pressurized container: May burst if heated.
---------	------------	---

Health Hazards

Skin irritation	Category 2	H315: Causes skin irritation.
Serious eye irritation	Category 2	H319: Causes serious eye irritation.
Skin sensitizer	Category 1	H317: May cause an allergic skin reaction.
Specific Target Organ Toxicity - Single Exposure	Category 3	H336: May cause drowsiness or dizziness.
Aspiration Hazard	Category 1	H304: May be fatal if swallowed and enters air- ways.

Environmental Hazards

Chronic hazards to the aquatic environment	Category 2	H411: Toxic to aquatic life with long lasting ef- fects.
---	------------	---

Hazard summary

Physical Hazards: Flammable aerosol.

Health Hazards

Inhalation: Has a narcotic effect.

Ingestion: If ingested, material may be aspirated into the lungs and cause chemical pneumonitis. Treat appropriately.

2.2 Label Elements

Contains: Hydrocarbons, low viscous
Isopropyl alcohol
Acetone
D-Limonene



Signal Words: Danger

Product name: RENOCLEAN MVE 6006

Hazard Statement(s): H222: Extremely flammable aerosol.
H229: Pressurized container: May burst if heated.
H315: Causes skin irritation.
H319: Causes serious eye irritation.
H317: May cause an allergic skin reaction.
H336: May cause drowsiness or dizziness.
H411: Toxic to aquatic life with long lasting effects.

Precautionary Statements

Prevention: P102: Keep out of reach of children.
P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211: Do not spray on an open flame or other ignition source.
P251: Do not pierce or burn, even after use.
P261: Avoid breathing dust/fume/gas/mist/vapors/spray.
P262: Do not get in eyes, on skin, or on clothing.
P273: Avoid release to the environment.
P280: Wear protective gloves/ protective clothing/ eye protection/ face protection.

Response: P333+P313: If skin irritation or rash occurs: Get medical advice/attention.

Storage: P410+P412: Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122°F.

Disposal: P501: Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.

2.3 Other hazards: By handling of mineral oil products and chemical products no particular hazard is known when normal precautions (item 7) and personal protective equipment (item 8) are kept. The product may not be released into the environment without control.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

General information: Mixture of active ingredients with propellant

Product name: RENOCLEAN MVE 6006

Chemical name	Identifier	Concentration *	UK-REACH Registration No.	Notes
Hydrocarbons, low viscous	EC: 921-024-6	50,00% - <100,00%		
Butane (<0,1% 1,3-butadiene)	EINECS: 203-448-7	0% - <100,00%		
Propane	EINECS: 200-827-9	0% - <100,00%		
Isobutane (<0,1% 1,3-butadiene)	EINECS: 200-857-2	0% - <100,00%		
Isopropyl alcohol	EINECS: 200-661-7	10,00% - <20,00%		
Acetone	EINECS: 200-662-2	10,00% - <20,00%		
D-Limonene	EINECS: 227-813-5	1,00% - <2,50%		

* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

PBT: persistent, bioaccumulative and toxic substance.

vPvB: very persistent and very bioaccumulative substance.

Classification

Chemical name	Identifier	Classification
Hydrocarbons, low viscous	EC: 921-024-6	GBCLP: Flam. Liq. 2;H225, Asp. Tox. 1;H304, Skin Irrit. 2;H315, STOT SE 3;H336, Aquatic Chronic 2;H411
Butane (<0,1% 1,3-butadiene)	EINECS: 203-448-7	GBCLP: Flam. Gas 1A;H220, Press. Gas Compr. Gas;H280
Propane	EINECS: 200-827-9	GBCLP: Flam. Gas 1A;H220, Press. Gas Compr. Gas;H280
Isobutane (<0,1% 1,3-butadiene)	EINECS: 200-857-2	GBCLP: Flam. Gas 1A;H220, Press. Gas Compr. Gas;H280
Isopropyl alcohol	EINECS: 200-661-7	GBCLP: Flam. Liq. 2;H225, Eye Irrit. 2;H319, STOT SE 3;H336
Acetone	EINECS: 200-662-2	GBCLP: Flam. Liq. 2;H225, Eye Irrit. 2;H319, STOT SE 3;H336 EUH066
D-Limonene	EINECS: 227-813-5	GBCLP: Flam. Liq. 3;H226, Skin Irrit. 2;H315, Skin Sens. 1B;H317, Asp. Tox. 1;H304, Aquatic Chronic 1;H410, Aquatic Acute 1;H400

GB-CLP

SECTION 4: First aid measures

General: Instantly remove any clothing soiled by the product.

4.1 Description of first aid measures

Inhalation: Supply fresh air; consult doctor in case of symptoms.

Eye contact: Immediately flush with plenty of water for at least 15 minutes. If easy to do, remove contact lenses. Get medical attention.

Skin Contact: Get medical attention. Destroy or thoroughly clean contaminated shoes. Immediately remove contaminated clothing and shoes and wash skin with soap and plenty of water. If skin irritation or an allergic skin reaction develops, get medical attention.

Product name: RENOCLEAN MVE 6006

Ingestion:	Call a physician or poison control center immediately. Rinse mouth. Never give liquid to an unconscious person. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs. Do NOT induce vomiting. Call a POISON CENTER or doctor/ physician if you feel unwell.
4.2 Most important symptoms and effects, both acute and delayed:	Suspected to cause hypersensitivity and allergy. Causes serious eye irritation. Causes skin irritation. If ingested, material may be aspirated into the lungs and cause chemical pneumonitis. Treat appropriately. Dizziness Freeze burns
4.3 Indication of any immediate medical attention and special treatment needed	Symptoms may be delayed.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media: CO₂, fire extinguishing powder or fog like water spraying. Extinguish larger fires with alcohol resistant foam or spray water with suitable surfactant added

Unsuitable extinguishing media: Water with a full water jet.

5.2 Special hazards arising from the substance or mixture:

Danger of explosion with aerosol cans.

5.3 Advice for firefighters

Special fire-fighting procedures: Move container from fire area if it can be done without risk. Dispose of fire debris and contaminated fire fighting water in accordance with official regulations. Collect contaminated fire fighting water separately. It must not enter drains.

Special protective equipment for fire-fighters: Self-contained breathing apparatus and full protective clothing must be worn in case of fire.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures: Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Keep unauthorized personnel away.

6.2 Environmental Precautions: Avoid release to the environment. Prevent further leakage or spillage if safe to do so.

6.3 Methods and material for containment and cleaning up: Scrape up spillage or absorb with absorbing material. Stop the flow of material, if this is without risk. Dispose of the material collected according to regulations.

6.4 Reference to other sections: See Section 8 of the SDS for Personal Protective Equipment. See Section 7 for information on safe handling See Section 13 for information on disposal.

Product name: RENOCLEAN MVE 6006

Dike for later disposal. Prevent entry into waterways, sewer, basements or confined areas. Stop the flow of material, if this is without risk.

SECTION 7: Handling and storage:

- 7.1 Precautions for safe handling:** Avoid contact with eyes. Wash hands thoroughly after handling. Do not eat, drink or smoke when working with the product. Take usual precautions when handling mineral oil products or chemical products. Avoid contact with skin. Avoid contact with eyes, skin, and clothing. Avoid contact with flame and heat source, prevent contact with direct sunlight Use only in well-ventilated areas.
- 7.2 Conditions for safe storage, including any incompatibilities:** Store locked up. Local regulations concerning handling and storage of waterpolluting products have to be followed. Local regulations for the storage and handling of aerosol cans and flammable liquids have to be kept. Keep away from heat/sparks/hot surfaces. - No smoking.
- 7.3 Specific end use(s):** Not applicable
- Storage Class:** 2 B, Aerosols

SECTION 8: Exposure controls/personal protection

8.1 Control Parameters

Occupational Exposure Limits

8.2 Exposure controls

- Appropriate engineering controls:** Provide adequate ventilation. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Individual protection measures, such as personal protective equipment

- General information:** Wash hands before breaks and after work. Use personal protective equipment as required. Personal protection equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment. The usual precautionary measures should be adhered to in handling the chemicals or the mineral oil products.
- Eye/face protection:** Safety glasses (EN 166) recommended during refilling. Avoid contact with eyes. Avoid contact with skin and eyes. Goggles/face shield are recommended. If risk of splashing, wear safety goggles or face shield. Avoid contact with skin and eyes. Goggles/face shield are recommended. If risk of splashing, wear safety goggles or face shield.

Product name: RENOCLEAN MVE 6006

Skin protection

Hand Protection:

Material: Nitrile butyl rubber (NBR).
Min. Breakthrough time: ≥ 480 min
Recommended thickness of the material: $\geq 0,38$ mm

Avoid long-term and repeated skin contact. Suitable gloves can be recommended by the glove supplier. Use skin protection cream for preventive skin protection. Protective gloves, where permitted in acc. to safety directions. The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

Other:

Do not carry cleaning cloths impregnated with the product in trouser pockets. Wear suitable protective clothing.

Respiratory Protection:

Ensure good ventilation/exhaustion at the workplace. Avoid breathing vapour/ aerosol.

Thermal hazards:

Not known.

Hygiene measures:

Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing to remove contaminants. Discard contaminated footwear that cannot be cleaned.

Environmental Controls:

No data available.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance

Physical state:

Aerosol

Form:

Aerosol

Color:

Colourless

Odor:

No data available.

pH:

substance/mixture is non-soluble (in water)

Freezing point:

not determined

Boiling Point:

not determined

Flash Point:

< 0 °C

Evaporation Rate:

Not applicable for mixtures

Flammability (solid, gas):

not determined

Explosion Limit - Upper (%):

Not applicable for mixtures

Explosion Limit - Lower (%):

Not applicable for mixtures

Vapor pressure:

Not applicable for mixtures

Relative vapor density:

Not applicable for mixtures

Density:

0,66 g/cm³ (15 °C)

Solubility(ies)

Solubility in Water:

No data available.

Solubility (other):

No data available.

Partition coefficient (n-octanol/water):

Not applicable for mixtures

Product name: RENOCLEAN MVE 6006

Auto-ignition temperature:	not determined
Decomposition Temperature:	not determined
Flow time	Value not relevant for classification
Explosive properties:	Value not relevant for classification
Oxidizing properties:	Value not relevant for classification
Particle characteristics:	Not applicable
9.2 Other information	No data available.

SECTION 10: Stability and reactivity

10.1 Reactivity:	Stable under normal use conditions.
10.2 Chemical Stability:	Stable under normal use conditions.
10.3 Possibility of hazardous reactions:	Stable under normal use conditions.
10.4 Conditions to avoid:	Stable under normal use conditions.
10.5 Incompatible Materials:	Strong oxidizing substances. Strong acids. Strong bases.
10.6 Hazardous Decomposition Products:	Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapors.

SECTION 11: Toxicological information

Information on likely routes of exposure

Inhalation:	No data available.
Ingestion:	No data available.
Skin Contact:	Causes skin irritation. May cause an allergic skin reaction.
Eye contact:	Causes eye irritation.

11.1 Information on toxicological effects

Acute toxicity

Oral

Product:	Not classified for acute toxicity based on available data. Not classified for acute toxicity based on available data.
Specified substance(s)	
Isopropyl alcohol	LD 50 (Rat): 4.570 mg/kg
Acetone	LD 50 (Rat): 5.800 mg/kg (OECD 401)

Product name: RENOCLEAN MVE 6006

Dermal

Product: Not classified for acute toxicity based on available data. Not classified for acute toxicity based on available data.

Specified substance(s)

Isopropyl alcohol LD 50 (Rabbit): 13.400 mg/kg

Acetone LD 50 (Rabbit): > 15.800 mg/kg

Inhalation

Product: Not classified for acute toxicity based on available data. Not classified for acute toxicity based on available data.

Specified substance(s)

Butane (<0,1% 1,3-butadiene) LC 50 (Rat, 4 h): 658 mg/l
Gas

Isopropyl alcohol LC 50 (Rat, 4 h): 30 mg/l

Acetone LC 50 (Rat, 4 h): 76 mg/l

Skin Corrosion/Irritation:

Product: Based on available data, the classification criteria are met.

Specified substance(s)

Acetone
Prolonged skin contact may cause redness, irritation and dry skin.

Serious Eye Damage/Eye Irritation:

Product: Based on available data, the classification criteria are met.

Specified substance(s)

Acetone
OECD 405 (Rabbit):
Causes serious eye irritation.

Respiratory or Skin Sensitization:

Product: Skin sensitizer: Based on available data, the classification criteria are met.
Respiratory sensitizer: Based on available data, the classification criteria are not met.

Specified substance(s)

Acetone
Based on available data, the classification criteria are not met.

Germ Cell Mutagenicity

Product: Based on available data, the classification criteria are not met.

In vitro

Specified substance(s)

Acetone
Based on available data, the classification criteria are not met.

In vivo

Specified substance(s)

Acetone
Based on available data, the classification criteria are not met.

Carcinogenicity

Product: Based on available data, the classification criteria are not met.

Product name: RENOCLEAN MVE 6006

Specified substance(s)

Acetone

Based on available data, the classification criteria are not met.

Reproductive toxicity

Product:

Based on available data, the classification criteria are not met.

Specific Target Organ Toxicity - Single Exposure

Product:

Based on available data, the classification criteria are met.

Specified substance(s)

Acetone

May cause drowsiness or dizziness.

Specific Target Organ Toxicity - Repeated Exposure

Product:

Based on available data, the classification criteria are not met.

Specified substance(s)

Acetone

Based on available data, the classification criteria are not met.

Aspiration Hazard

Product:

May be fatal if swallowed and enters airways.

Other adverse effects:

No data available.

SECTION 12: Ecological information

General information:

Not applicable

12.1 Toxicity

Acute toxicity

Product:

Based on available data, the classification criteria are not met.

Fish

Specified substance(s)

Hydrocarbons, low viscous

LC 50 (Fish, 96 h): 11,4 mg/l (OECD 203)

Propane

LC 50 (Fish, 96 h): > 1.000 mg/l

Isobutane (<0,1% 1,3-butadiene)

LC 50 (Fish, 96 h): 28 mg/l

Isopropyl alcohol

LC 50 (Fish, 96 h): 9.640 mg/l

Acetone

LC 50 (Fish, 96 h): 5.540 mg/l

Aquatic Invertebrates

Specified substance(s)

Hydrocarbons, low viscous

LC 50 (Water Flea, 48 h): 3 mg/l (OECD 202)

Isobutane (<0,1% 1,3-butadiene)

EC 50 (Water Flea, 48 h): 16,3 mg/l

Isopropyl alcohol

LC 50 (48 h): 1.400 mg/l

Product name: RENOCLEAN MVE 6006

Acetone EC 50 (Water Flea, 48 h): 8.800 mg/l

Chronic Toxicity

Product: Based on available data, the classification criteria are met.

Toxicity to Aquatic Plants

Specified substance(s)

Hydrocarbons, low vis-
cous LC 50 (Alga, 72 h): 30 mg/l (OECD 201)

Isobutane (<0,1% 1,3-
butadiene) EC 50 (Alga, 72 h): 8,6 mg/l

Isopropyl alcohol LC 50 (Alga, 72 h): > 100 mg/l

12.2 Persistence and Degradability

Biodegradation

Product: Not applicable for mixtures

Specified substance(s)

Acetone The product is easily biodegradable.

12.3 Bioaccumulative potential

Product: Not applicable for mixtures

Specified substance(s)

Acetone Bioconcentration Factor (BCF): 0,69 The product is not bioaccumulating.

12.4 Mobility in soil:

Product: Not applicable for mixtures

**12.5 Results of PBT and vPvB
assessment:**

The product does not contain any substances fulfilling the PBT/vPvB criteria.

12.6 Other adverse effects:

Toxic to aquatic life with long lasting effects.

**Water Hazard Class
(WGK):**

WGK 1: slightly water-endangering.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

General information: Dispose in accordance with all applicable regulations.

Disposal methods: Discharge, treatment, or disposal may be subject to national, state, or local laws.

List of Waste (LoW) Codes

16 05 04*: Gases in pressure containers (including halons) containing hazardous substances.

Product name: RENOCLEAN MVE 6006

SECTION 14: Transport information

ADR/RID

14.1 UN number or ID number:	UN 1950
14.2 UN Proper Shipping Name:	AEROSOLS
14.3 Transport Hazard Class(es)	
Class:	2
Label(s):	2.1
Hazard No. (ADR):	–
Tunnel restriction code:	(D)
14.4 Packing Group:	–
14.5 Environmental hazards:	–
14.6 Special precautions for user:	–

IMDG

14.1 UN number or ID number:	UN 1950
14.2 UN Proper Shipping Name:	AEROSOLS
14.3 Transport Hazard Class(es)	
Class:	2.1
Label(s):	2.1
EmS No.:	F-D, S-U
14.3 Packing Group:	–
14.5 Environmental hazards:	–
14.6 Special precautions for user:	–

IATA

14.1 UN number or ID number:	UN 1950
14.2 Proper Shipping Name:	Aerosols, flammable
14.3 Transport Hazard Class(es):	
Class:	2.1
Label(s):	2.1
14.4 Packing Group:	–
14.5 Environmental hazards:	–
14.6 Special precautions for user:	–

14.7 Transport in bulk according to Annex II of MARPOL and the IBC Code: Not applicable.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture:

GB Regulations

The Ozone-Depleting Substances and Fluorinated Greenhouse Gases (Amendment etc.) (EU Exit) Regulations 2019:
none

The Persistent Organic Pollutants (Amendment) (EU Exit) Regulations 2020:
none

15.2 Chemical safety assessment: No Chemical Safety Assessment has been carried out.

Product name: RENOCLEAN MVE 6006

DIRECTIVE Control of Major Accident Hazards Regulations 2015:

The product falls into the scope of the Control of Major Accident Hazards Regulations 2015.

Hazard category in accordance with GB-CLP	Qualifying quantity for the application of Lower-tier requirements:	Qualifying quantity for the application of Upper-tier requirements:
P3a: P3a. Flammable aerosols	150 t	500 t
E2: E2. Hazardous to the aquatic environment	200 t	500 t

SECTION 16: Other information

Revision Information: Vertical lines in the margin indicate an amendment.

Wording of the H-statements in section 2 and 3

EUH066	Repeated exposure may cause skin dryness or cracking.
H220	Extremely flammable gas.
H222	Extremely flammable aerosol.
H225	Highly flammable liquid and vapor.
H226	Flammable liquid and vapor.
H229	Pressurized container: May burst if heated.
H280	Contains gas under pressure; may explode if heated.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H411	Toxic to aquatic life with long lasting effects.

Other information: The classification complies with the current GB lists; however, it has been supplemented with expert literature information and information provided by/about our company. The following evaluation methods were used: On the basis of test data; Calculation Method; Bridging Principle "Substantially similar mixtures"; Expert Judgement

Revision Date: 24.10.2024

Disclaimer: The data contained in this safety data sheet are based on our current knowledge and experience and are given to the best of our knowledge and belief. It characterizes the product only with regard to safety requirements for handling, transport and disposal. The data do not describe the product's properties (tech. product specification). Neither should any agreed property nor the suitability of the product for any specific technical application be deduced from the data contained in this safety data sheet. Modifications on this document are not allowed. The data are not transferable to other products. In the case of mixing the product with other products or in the case of processing, the data in this safety data sheet are not necessarily valid for the new-made material. It is the responsibility of the recipient of the product to observe federal, state and local law. Please contact us to obtain up-to-date safety data sheets. This document was issued electronically and has no signature.