



Part Number : [15311043](#)
Product Description : 4.80mm Pitch Wire-to-Wire
Plug Housing, 4 Circuits
Series Number : 5025
Status : Active
Product Category : Connector Housings
Engineering Number : 5025-04P1



Documents & Resources

Drawings

[015311043_sd.pdf](#)
[SPK-5025-001-001.pdf](#)

3D Models and Design Files


[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications

[PS-5025-001-001.pdf](#)
[PS-5025-002-001.pdf](#)
[PS-5025-003-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	5025
Description	4.80mm Pitch Wire-to-Wire Plug Housing, 4 Circuits
Application	Power, Wire-to-Wire
Product Name	N/A
UPC	800754214032

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	4
Flammability	94V-2
Gender	Plug
Glow-Wire Capable	No
Net Weight	1567.400/mg
Number of Rows	1
Packaging Type	Bag

Panel Mount	No
Pitch - Mating Interface	4.80mm
Pitch - Termination Interface	4.80mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
4.80mm Pitch Wire-to-Wire Receptacle Housing, 4 Circuits	<u>15311042</u>

Use with Part(s)

Description	Part Number
4.80mm Pitch Male Crimp Terminal	<u>5006</u>