


## PASE12-XL

### Plummer block housing unit

Plummer block housing units PASE, cast iron housing, radial insert ball bearing with eccentric locking collar, P seals

X-life

## Technical information



### Your current product variant

Material	GG	Grey cast iron
----------	----	----------------

### Main Dimensions & Performance Data

d	12 mm	Bore diameter
L	125 mm	Length total
H <sub>2</sub>	57 mm	Height
≈m	0.45 kg	Weight

### Mounting dimensions

J	95 mm	Distance fixing bore
N	11 mm	Width (slot)
N <sub>1</sub>	19 mm	Length (slot)

### Dimensions

H	30.2 mm	Distance shaft axis
A	30 mm	Width (base)
A <sub>1</sub>	18 mm	Width (head)
H <sub>1</sub>	10 mm	Height (base)
B <sub>1</sub>	28.6 mm	Locking collar total width
S <sub>1</sub>	22.1 mm	Distance of raceway to locking collar
Q	M6	Connection thread for lubrication



Additional information

ASE03	Housing
GRAE12-XL-NPP-B	Bearing designation

Temperature range

T <sub>min</sub>	-20 °C	Operating temperature min.
T <sub>max</sub>	120 °C	Operating temperature max.