

## Han PE module male crimp 10qmm




Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 14 001 3071  |
| Specification      | Han PE module male crimp 10qmm  |
| HARTING eCatalogue | <a href="https://harting.com/09140013071">https://harting.com/09140013071</a> |

### Identification

|                    |                |
|--------------------|----------------|
| Category           | Modules        |
| Series             | Han-Modular®   |
| Type of module     | Han® PE module |
| Size of the module | Single module  |

### Version

|                    |   |
|--------------------|---|
| Termination method | Crimp termination   |
| Gender             | Male  |
| Number of contacts | 1   |
| Pack contents      | 2 PE module halves<br>1 contact pressure plate<br>1 crimp contact |

### Technical characteristics

|                         |                    |
|-------------------------|--------------------|
| Conductor cross-section | 10 mm <sup>2</sup> |
| Wire outer diameter     | ≤14.5 mm           |
| Contact resistance      | ≤0.3 mΩ            |
| Stripping length        | 19 mm              |
| Tightening torque       | 2 Nm               |
| Limiting temperature    | -40 ... +125 °C    |
| Mating cycles           | ≥500               |

### Material properties

|                   |                              |
|-------------------|------------------------------|
| Material (insert) | Zinc die-cast, nickel-plated |
|-------------------|------------------------------|



Pushing Performance  
Since 1945

## Material properties

|                                      |  |
|--------------------------------------|--|
| Material (contacts)                  | Copper alloy   |
| Surface (contacts)                   | Silver plated  |
| RoHS                                 | compliant with exemption                               |
| RoHS exemptions                      | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                           | compliant with exemption                               |
| China RoHS                           | 50   |
| REACH Annex XVII substances          | Not contained  |
| REACH ANNEX XIV substances           | Not contained  |
| REACH SVHC substances                | Yes  |
| REACH SVHC substances                | Lead   |
| ECHA SCIP number                     | 5dbb3851-b94e-4e88-97a1-571845975242                   |
| California Proposition 65 substances | Yes  |
| California Proposition 65 substances | Lead   |

## Specifications and approvals

|                |  |
|----------------|--|
| Specifications | IEC 61984  |
| UL / CSA       | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |

## Commercial data

|                                |   |
|--------------------------------|---|
| Packaging size                 | 1   |
| Net weight                     | 73.533 g  |
| Country of origin              | Germany   |
| European customs tariff number | 85389099  |
| GTIN                           | 5713140184886   |
| eCl@ss                         | 27440217 Module for industrial connectors (power/signals) |
| ETIM                           | EC000438  |
| UNSPSC 24.0                    | 39121552  |