




Terminals & Splices > Splices



Splice Type: 3-Way Splice

Wire Size: 1.25 – 2 mm²

Sealable: No

Splice Features: Heavy Duty, Serrated

Features

Product Type Features

Splice Accessory Type	Splice
Splice Type	3-Way Splice
Sealable	No
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Insulation Material	Nylon
Splice Features	Heavy Duty, Serrated
Primary Product Color	Blue

Contact Features

Contact Base Material	Copper
Barrel Type	Closed

Mechanical Attachment

--	--

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	2050 – 5180 CMA
Compatible Insulation Diameter Range	4.32 mm[.17 in]
Terminal Material Thickness	.79 mm[.031 in]

Usage Conditions

Insulation Option	Fully Insulated
-------------------	-----------------

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Also in the Series | **PLASTI-GRIP**




Compression Connectors(3)




Crimp Wire Pins, Tabs & Ferrules(20)



Ring Terminals(310)




Spade Terminals(158)




Splices(45)


Customers Also Bought




TE Part #1586841-4
VAL-U-LOK SKT 16AWG PHBZAU LP




TE Part #2176248-3
TJT 250W 2R2 5%




TE Part #1879662-9
H8 12R1 0.1% 15PPM




TE Part #7-2176369-9
RQ 0603 261R 0.1% 10PPM 5K RL




TE Part #1-499923-2
064 UNIV HDR SP 4S 15DP STD L1



TE Part #5-2176363-1
RQ 0402 1K43 0.1% 10PPM 5K RL



TE Part #T1010033100-000
H3A-KDBM



TE Part #8-2176370-3
RQ 0603 3K09 0.1% 10PPM 5K RL



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_34073_J.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_34073_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_34073_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English