

Features

- High crack resistance
- Chemically resistant
- Aluminum alloy housing design
- Articulated arm for precise positioning
- High quality LED
- Low power consumption
- Low heat emission design

RS PRO Machine Lighting

RS Stock No.: 0186235



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

The LED Machine Work Light is an advanced lighting solution designed for industrial settings. Engineered for durability and precision, it features high crack resistance and chemical resistance with an aluminium alloy housing. The articulated arm allows for precise positioning, while high-quality LEDs ensure bright illumination. With low power consumption and minimal heat emission, it is suitable for assembly and inspection tasks, machine installations, workshops, workstations, and clean rooms, providing enhanced visibility and safety.

General Specifications

Lamp Type	LED
Light Style	Machine Work Light
Luminosity	1100lm
Lumen Efficiency	110lm/W
Colour Temperature	5700K
Beam Angle	60°
Material	Aluminium
Finish	Silver
Duration	30000h
Lamp Supplied	Yes

Electrical Specifications

Wattage	10W
Voltage Rating	220-240VAC
Running Current	0.05A
Cable Entry	UK PLUG
Insulation Class	Class I

Mechanical Specifications

Fitting Type	Surface Mounted
Weight	2.5kg

Operation Environment Specifications

Environment Temperature	-20°C ~ +50°C
-------------------------	---------------

Protection Category

IP Rating	IP65
-----------	------

Approvals

Compliance/Certifications	CE
EU Energy Efficiency Rating	E
Declarations	UKCA, RoHS

SAFETY INFORMATION

The work light has been designed to meet the latest standard and manufactured with high-quality materials, tested by standard process. Still, the use of the product may constitute a risk to persons or cause material damage.

Explosion hazard

This lamp is not designed for use in flammable and explosive areas. Do not operate the lamp in hazardous location.

Electrical Safety

Compare the mains voltage with the nominal voltage and the hertz specified on the product and make sure that they are identical. Do not connect a damaged cable.

Bright light source exposure risk

Placed the lighting in an angle to avoid looking directly into the light source. Do not look directly into the light source.

Ambient temperature

The allowed ambient temperature for the light will be around 40°C. Avoid direct exposure to the sunlight.

INSTALLATION OF THE LAMP

Mounting

The light must be mounted on a stable, non-flammable surface with the included screws. The user must verify the reliability when using mounting elements which have not been proposed by the manufacturer.

Putting into operation

Before operating the light, please check whether the mains voltage is identical to the rated voltage specified on the rating plate.

MAINTENANCE AND REPAIR

Disconnect the light from the power source before carrying out any maintenance or repair work. This work may only be carried out by a qualified electrician! Disconnect a damaged connecting cable immediately from the power supply and have it replaced by the manufacturer or by a qualified electrician. Only parts approved by the manufacturer may be used as spare parts.

Cleaning

Clean the transparent shade regularly to ensure maximum brightness. Please use a cloth impregnated with a normal household detergent to clean the lamp components. Please ensure that the detergent used are compatible with paints and plastics.

