



E32-T11N 2M

Fiber optic sensor head, through-beam, M4 hexagonal back, right-angled head, R1 flexible fiber, 2 m cable

Specifications

Sensing method	Through-beam
Shape	Threaded
Size	M4
Application	Object detection
Features	90° cable exit, Flexible fiber, Hexagonal back
Temperature range	-40-70 °C
Sensing distance	3000 mm
Cable length	2 m
Bending radius	1 mm
Free cut	✓
Material core	Plastic
Degree of protection (IP)	IP67
Sensing surface orientation	Right-angle
Material sheath	PVC

Accessories



E39-F1

Long-distance lens unit for E32 through-beam fibers with M2.6 thread

Related products



E3X-ZV and E3X-MZV

Smart Fiber Amplifier



E3NX-CA

High-performance color mark sensor



E3NX-CA

High-performance color mark sensor



E3NX-MA

Smart Fiber Amplifier Units



E3NX-FA

High-performance digital fiber amplifier



E3X-NA

Digital fiber amplifier with potentiometer adjustment

Downloads

CAD Library



EAC Mark removal Discontinuation Notice

EN PDF 221 KB



Fiber Sensor Selection Selection Guide

EN PDF 16.2 MB

