

Wiha Professional electric.

Completely reliable.

Diagonal cutters.



Z 12 0 06

Diagonal cutters Professional electric.

Individually tested protective insulation 1,000 V AC, VDE and GS tested.

Standards: DIN ISO 5749.

Manufactured acc. to IEC 60900:2012.

Head shape: Semi-circular, swedish style.

Design: Low wear lap joint, riveted and able to withstand high loads. Lightweight action, clean cutting achieved by specially milled precision cutting edges. Long term cutting is achieved through additional inductive hardening to approx. 64 HRC. The Wiha DynamicJoint® ensures optimal transmission of hand strength to the cutting edges.

Material: High quality C 70 tool steel, tempered.

Application: Universal cutter for cutting soft and hard wires and cables, also suitable for cutting and stripping cables. For all work on or around electrical components up to 1,000 V AC.

Order-No.	mm	II	○	●	●	●	g	SB	≡
26737	140	5 ½	4.0	2.5	1.8	1.4	160		5
27428	140	5 ½	4.0	2.5	1.8	1.4	160	x	5
26741	160	6 ½	4.0	2.8	2.0	1.6	200		5
27429	160	6 ½	4.0	2.8	2.0	1.6	200	x	5
26744	180	7	4.0	3.0	2.5	1.8	250		5
27430	180	7	4.0	3.0	2.5	1.8	250	x	5



Z 16 0 06

Heavy duty diagonal cutters Professional electric.

Individually tested protective insulation 1,000 V AC, VDE and GS tested.

Standards: DIN ISO 5749.

Manufactured acc. to IEC 60900:2012.

Head shape: Semi-circular.

Design: Low wear lap joint, riveted and able to withstand high levels of load. Lightweight action, clean cutting achieved by specially milled precision cutting edges. Long term cutting is achieved through additional inductive hardening to approx. 64 HRC. The Wiha DynamicJoint® ensures optimal transmission of hand strength to the cutting edges.

Material: High quality C 70 tool steel, tempered.

Application: Power-assisted all-round diagonal cutter for cutting soft to extremely hard wires and cables. For all work on or around electrical components up to 1,000 V AC.

Order-No.	mm	II	○	●	●	g	SB	≡
26748	160	6 ½	3.5	2.5	2.0	190		5
27432	160	6 ½	3.5	2.5	2.0	190	x	5
26751	180	7	3.8	2.7	2.3	260		5
27434	180	7	3.8	2.7	2.3	260	x	5
26754	200	8	4.2	3.0	2.5	315		5
27435	200	8	4.2	3.0	2.5	315	x	5

Diagonal cutters.



NEW

Z 18 0 06

BiCut Professional electric - switchable high-performance diagonal cutters.

Individually tested protective insulation 1,000 V AC, VDE and GS tested.

Standards: Based on DIN ISO 5749.

Head shape: Semi-circular.

Design: Clever - BiCut does the job of two pairs of pliers. Powerful - Up to 50% less hand strength required for cutting. Power - Cutting force doubled for extremely hard materials. Comfortable - Easily switch between the two strengths in a one handed operation. Robust and durable - Cutter blades induction hardened up to 64 HRC.

Material: Hard as steel - Drop forged of high-quality C70 steel.

Application: For cutting various materials from soft to extremely hard, such as cables, nails, screws, bolts, wire cable, spring wire, chains, etc. For all work on or around electrical components up to 1,000 V AC.

Order-No.	mm	II	○	●	g	SB	≡
38191	200	8	3.5	3	350		5
38984	200	8	3.5	3	350	x	5



Z 14 0 06

Electrician's diagonal cutters Professional electric.

Individually tested protective insulation 1,000 V AC, VDE and GS tested.

Standards: DIN ISO 5749.

Manufactured acc. to IEC 60900:2012.

Head shape: Semi-circular, swedish style.

Design: Low wear lap joint, riveted and able to withstand high loads. The Wiha DynamicJoint® ensures optimal transmission of hand strength to the cutting edges. Lightweight action, clean cutting achieved by specially milled precision cutting edges. Long term cutting is achieved through additional inductive hardening to approx. 64 HRC. Rear cutting area near to plier joint also suitable for medium-hard and hard wire. Front cutting area for soft wire, with precision stripping stations for 1.5 mm² and 2.5 mm² single-wire conductor.

Material: High quality C 70 tool steel, tempered.

Application: Special diagonal cutters with additional function for electrical installation. For all work on or around electrical components up to 1,000 V AC.

Order-No.	mm	II	○	●	●	g	SB	≡
26745	160	6 ½	4.0	2.0	1.6	200		5
27431	160	6 ½	4.0	2.0	1.6	200	x	5