

926305-1 ✓ ACTIVE

MATE-N-LOK | Universal MATE-N-LOK


TE Internal #: 926305-1

4 Position, Cap, Housing, Crimp, Wire-to-Panel / Wire-to-Wire, UL 94V-2, 6.35 mm [.25 in] Centerline, 1 Row, 600 VAC, Universal MATE-N-LOK

[View on TE.com >](#)



Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**

Connector & Housing Type: **Cap**

Termination Method to Wire & Cable: **Crimp**

Connector System: **Wire-to-Panel, Wire-to-Wire**

Contact Retention Within Housing: **Without**

## Features

### Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Cap
Connector System	Wire-to-Panel, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Number of Positions	4
Number of Rows	1
Number of Power Positions	0
Number of Signal Positions	0

### Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

### Body Features

Primary Product Color	Natural
-----------------------	---------

### Contact Features

Multiple Contact Types	Without
Contact Layout	Inline
Contact Retention Within Housing	Without
Contact Type	Pin

### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

### Mechanical Attachment

Panel Mount Feature	With
Panel Mount Feature Type	Latches
Connector Mounting Type	Panel Mount

### Housing Features

Centerline (Pitch)	6.35 mm [.25 in]
Housing Material	PA 6.6

### Dimensions

Panel Thickness (Recommended)	.76 – 2.29 mm [.03 – .09 in]
-------------------------------	------------------------------

### Usage Conditions

Operating Temperature Range	-55 – 125 °C [-67 – 257 °F]
-----------------------------	-----------------------------

### Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

### Industry Standards

Compatible With Agency/Standards Products	VDE
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
UL Flammability Rating	UL 94V-2
Glow Wire Rating	Standard Part - Not Glow Wire

### Packaging Features

Packaging Quantity	500
Packaging Method	Bag

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 926298-5  
UN-MNL STECK-GEH 4P



TE Part # 350584-1  
04P UMNL PIN HDR ASSY V2 NATL



TE Part # 350584-4  
04P UMNL PIN HDR ASSY V2 LF



TE Part # 1586852-1  
04P UMNL PLUG HSG, GW



TE Part # 1-350779-9  
04P UMNL V0 PLUG HSG BLACK



TE Part # 1-480702-1  
04P UMNL PLUG HSG BRN



TE Part # 2029387-1  
04P UMNL SHORT LATCH PLUG V0



TE Part # 1-350948-0  
04P UMNL HDR ASSY R/A V2 NATL




TE Part # 1586872-1  
04P UMNL HDR ASSY, GW



TE Part # 350779-4  
04P UMNL PLUG HSG UL94VO



TE Part # 643416-1  
04P UMNL HDR ASSY POL 94VO



TE Part # 770019-1  
04P UMNLII IN-LNE PLUG HSG KIT



TE Part # 1-480702-2  
04P UMNL PLUG HSG RED



TE Part # 1586076-1  
02P UMNL PIN HDR W/O DRNS V2



TE Part # 926682-3  
06P UNIV.M-N-L.HSG.



TE Part # 926298-7  
UNIVERSAL MATE-N-LOK 4 WAY PLUG



TE Part # 770035-1  
04P UMNL II PLUG-FRONT 94VO



TE Part # 926298-6  
UNML PLUG 4WAY



TE Part # 1703062-1  
CAP, 2 CIRCUIT, UNIVERSAL MATE-N-LOK



TE Part # 350761-5  
04P UMNL HDR ASSY PC LF

Also in the Series | **Universal MATE-N-LOK**



Circular Power Connectors(2)



Connector Contacts(213)



Power Contacts(213)



Rectangular Connector Housings(364)




Rectangular Power Connectors(646)



Standard Circular Connectors(1)




Standard Rectangular Connectors(365)



Wire-to-Board Connector Assemblies & Housings(117)

Customers Also Bought



## Documents

### Product Drawings

#### 4P UNIV M-N-L CAP

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_926305-1\\_H.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_926305-1\\_H.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_926305-1\\_H.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

## Product Specifications



### Application Specification

English

---

### Agency Approvals

UL

English