





All Metal Exterior, Elbow - ASB ASB2201-G01-08

Datasheet

General series information


- Environments with welding spatter, dust and ultraviolet radiation
- Port Size: M5, 10-32 UNF, 1/8, 1/4, 3/8, 1/2
- Applicable Tubing O.D.: Ø 4 to Ø 12 mm and Ø 5/32" to Ø 1/2"
- Operating Pressure Range: 0.1 to 1 MPa.




Flow control valve, adjustable, with reverse free flow

Standard specifications

Body Size	2 (1/8, 1/4)
Control Type	0 (Meter-out)
Thread Type	G (G)
Port Size	01 (1/8)
Applicable Tubing O.D.	08 (ø8)
Seal Method	w/o Sealant
Option	Electroless Nickel Plating
Lock Nut	Hexagon Lock Nut
Pressure medium	Air
Maximum operating pressure	1 MPa
Minimum operating pressure	0.1 MPa
Proof pressure	1.5 MPa
Maximum ambient temperature	60 °C
Minimum ambient temperature	-5 °C
Applicable tubing material	FEP, PFA, Nylon, Soft nylon, Polyurethane, Polyolefin
Weight	0.026 Kg



Constructions



Component Parts

No.	Description	Material	Note	
1	Body A	Zinc alloy		
2	Body B	Brass	Electroless nickel plating*1	
3	Needle	Brass	Electroless nickel plating*1	
4	Knob	Brass	Electroless nickel plating*1	
5	Lock nut	Brass	Meter-out	Electroless nickel
			Meter-in	Black zinc chromate
6	C-ring	Stainless steel		
7	Seat ring	Brass	Electroless nickel plating	
8	O-ring	NBR		
9	U-seal	HNBR		
10	O-ring	NBR		
11	Seal	FKM		
12	Cover	Stainless steel		
13	Cassette	Stainless steel		
15	Seal	NBR	G thread type	

*1 Option B specifies the body without electroless nickel plating.

Additional information

Catalogue

[ASB_EU.pdf](#)

Operation manuals

[OM_ASB_OMZ0085EN-C.pdf](#)