

## Protective covers - HC-B16-HCLWD-PLR-BK - 1414639


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Protective cover B16, with double locking latch, protective cover material: PA, height: 21.6 mm, seal: yes, diameter of retaining cord eyelet: 30 mm



### Key Commercial Data

Packing unit	10 pc
GTIN	 4 055626 131337
GTIN	4055626131337
Weight per Piece (excluding packing)	60.210 g
Custom tariff number	85389099
Country of origin	Poland

### Technical data

#### Dimensions

Length	93.5 mm
Width	43 mm
Height	21.6 mm
Diameter of retaining cord eyelet	30 mm

#### Ambient conditions

Degree of protection (IP)	IP66
Ambient temperature (operation)	-20 °C ... 100 °C

#### General

Size	B16
Material	PA
Seal material	NBR
Flammability rating according to UL 94	HB
Color	black
Seal present	yes

## Protective covers - HC-B16-HCLWD-PLR-BK - 1414639

### Technical data

#### General

Note	Protective cover for supporting base element for double locking latch
Connection	Plastic protective cover for short-term protection

#### Standards and Regulations


Flammability rating according to UL 94	HB
--	----

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Drawings

Dimensional drawing



Dimensional drawing

### Classifications

#### eCl@ss

eCl@ss 4.0	23110100
eCl@ss 4.1	23110100
eCl@ss 5.0	23110100
eCl@ss 5.1	23110100
eCl@ss 6.0	27261200
eCl@ss 7.0	27440208
eCl@ss 8.0	27440208
eCl@ss 9.0	27440208

#### ETIM

ETIM 5.0	EC002314
ETIM 6.0	EC002314
ETIM 7.0	EC002314

## Protective covers - HC-B16-HCLWD-PLR-BK - 1414639

### Classifications

#### UNSPSC

UNSPSC 13.2	39121421
UNSPSC 18.0	39121421
UNSPSC 19.0	39121421
UNSPSC 20.0	39121421
UNSPSC 21.0	39121421

### Approvals


#### Approvals

#### Approvals

#### EAC

#### Ex Approvals

#### Approval details

EAC		RU C- DE.AI30.B.01102
-----	---	--------------------------