


FEATURES

- **Material Composition:** Made from Fluorinated Ethylene Propylene, Fluoroelastomer, and Viton for enhanced chemical resistance
- **Temperature Range:** Operates effectively between -20 °C and 140 °C, suitable for extreme conditions
- **Hardness:** Shore A 90 to 95 ensures durability and a tight seal
- **Size Specifications:** Inside diameter of 129.54 mm and outside diameter of 140.2 mm for precise fitting
- **Thickness:** 5.33 mm provides robust sealing capability

RS PRO 129.54 mm O-Ring Seal, Shore A 90 to 95

RS Stock No: 731-408



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO O-Ring Seal is designed for reliable sealing in various industrial applications. Constructed from high-quality materials such as Fluorinated Ethylene Propylene, Fluoroelastomer, and Viton, it offers excellent resistance to chemicals and high temperatures, making it ideal for demanding environments.

General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

Mechanical Specifications

Inside Diameter	129.54 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	140.2 mm
Thickness	5.33 mm

Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	---

