




Diffuse reflection sensor

OTT-FPKG/US-100-IPF



receiver in lower lens
transmitter in upper lens



Product characteristics		
Type of light		infrared light
Housing		rectangular
Application		
Function principle		Diffuse reflection sensor
Electrical data		
Operating voltage	[V]	10...50 DC
Current consumption	[mA]	40; ((24 V))
Protection class		II
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	880
Outputs		
Electrical design		PNP
Output function		light-on/dark-on mode; (programmable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	150
Short-circuit protection		yes



Diffuse reflection sensor

OTT-FPKG/US-100-IPF

Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Range [mm]	4...200; (white paper 200 x 200 mm)
Range adjustable	yes
Max. light spot diameter [mm]	187
Light spot dimensions refer to	at maximum range

Operating conditions

Ambient temperature [°C]	-25...60
Protection	IP 65

Tests / approvals

EMC	EN 60947-5-2
MTTF [years]	583

Mechanical data

Weight [g]	146.5
Housing	rectangular
Dimensions [mm]	75 x 19 x 30
Materials	PBT
Lens material	PMMA
Lens alignment	side lens

Displays / operating elements

Display	switching status	1 x LED, yellow
	operation	1 x LED, green

Accessories

Items supplied	Angle bracket: 1, E20461
	screwdrivers

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A



Diffuse reflection sensor

OTT-FPKG/US-100-IPF

Connection



Diagrams and graphs

excess gain graph

