

AXL F LPEDO8/3 1F - Safety module



2702171

<https://www.phoenixcontact.com/in/products/2702171>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Axioline F, Digital output module, Functional safety, SafetyBridge solution, Digital outputs: 4 (for 2-channel assignment), 8 (for 1-channel assignment), 2 A, degree of protection: IP20

Product description

The safety module is an output module from the Axioline F product range with integrated safety logic designed for use in a SafetyBridge Technology V3 system. The safety module can be used as part of an Axioline F station at any point within an EtherCAT®, EtherNet/IP™, Sercos, Modbus, PROFINET or PROFIBUS system. The module has four safe digital outputs for two-channel assignment or eight safe digital outputs for single-channel assignment.

Your advantages

- Cost-effective system configuration, as no safety PLC or safe fieldbus system is required
- Flexible use, thanks to compatibility with all bus couplers from the Axioline F range
- Reduced installation time, thanks to fast wiring and easy handling
- Easy configuration using the free SAFECONF software
- Up to Cat. 4/PL e in accordance with EN ISO 13849-1, SIL 3 in accordance with EN IEC 62061, SIL 3 in accordance with IEC 61508

Commercial data

Item number	2702171
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DNA
Product key	DNA511
Catalog page	Page 269 (C-6-2019)
GTIN	4055626004983
Weight per piece (including packing)	352.9 g
Weight per piece (excluding packing)	222 g
Customs tariff number	85389091
Country of origin	DE

AXL F LPEDO8/3 1F - Safety module



2702171

<https://www.phoenixcontact.com/in/products/2702171>

Technical data

Dimensions

Dimensional drawing	
Width	53.6 mm
Height	126.1 mm
Depth	54 mm
Note on dimensions	Housing dimensions

Notes

Note on application	
Note on application	Only for industrial use

Interfaces

Axioline F local bus	
Connection method	Bus base module

System properties

SafetyBridge properties	
Connection to I/O modules	max. 16 (safe digital I/O modules)
Logic memory	30 kByte

Module	
Input address area	48 Byte
Output address area	48 Byte
Required parameter data	1 Byte
Required configuration data	7 Byte

Output data

Digital:	
Output name	Digital outputs
Number of outputs	4 (for 2-channel assignment)
	8 (for 1-channel assignment)
	8
Protective circuit	Overload protection, freewheeling circuit for inductive loads, Discharge circuit for accelerated discharge of capacitive loads

AXL F LPDO8/3 1F - Safety module



2702171

<https://www.phoenixcontact.com/in/products/2702171>

Output voltage	24 V DC
Output current	max. 2 A (per channel)
	max. 1.5 A (per channel according to CUL_{US})
	max. 4 A (per group)
	max. 3 A (per group according to CUL_{US})
	max. 8 A (Total current of all outputs; Please observe the notes in the user manual.)
	max. 6 A (Total current of all outputs according to CUL_{US})
Maximum output current per channel	2 A
Maximum output current per module / terminal block	8 A
Permissible cable length	max. 1000 m (Forward and return line in total)
Behavior with overload	Affected output is disabled and a diagnostic message is generated.

Product properties

Product type	I/O component
Product family	Axioline F
Application	Functional safety
	SafetyBridge
Type	modular

Electrical properties

Transmission medium	Copper
---------------------	--------

Potentials

Protective circuit	Protection against polarity reversal, EMC protective circuit, undervoltage detection
--------------------	--

Potentials: Axioline F local bus supply (U_{Bus})

Supply voltage	5 V DC (via bus base module)
Current draw	max. 280 mA
	typ. 260 mA (all outputs set; supply by U_O of 19.2 V DC ... 30 V DC)

Potentials: Supply for digital output modules (U_O)

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	typ. 25 mA (all outputs set; supply from U_O with 30 V DC; without supply to the actuators)

Connection data

Connection technology

Connection name	Axioline F connector
-----------------	----------------------

Conductor connection

Connection method	Spring-cage connection
Conductor cross section rigid	0.2 mm ² ... 1.5 mm ²

AXL F LPEDO8/3 1F - Safety module



2702171

<https://www.phoenixcontact.com/in/products/2702171>

Conductor cross section flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross section AWG	24 ... 16

Axioline F connector

Connection method	Spring-cage connection
Conductor cross section, rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross section, flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross section AWG	24 ... 16

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-35 °C ... 60 °C (Mounting position: any)
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 108 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (up to 3500 m above sea level)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	10 % ... 75 % (on average, 85% infrequently, non-condensing)
Permissible humidity (storage/transport)	10 % ... 75 % (non-condensing)

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

AXL F LPSDO8/3 1F - Safety module


2702171

<https://www.phoenixcontact.com/in/products/2702171>




Drawings

Dimensional drawing



Dimensions (in mm)

Connection diagram



Example connection of a contactor

AXL F LPEDO8/3 1F - Safety module



2702171

<https://www.phoenixcontact.com/in/products/2702171>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/2702171>



DNV GL

Approval ID: TAA00000DF

BSH

Approval ID: 840



Functional Safety

Approval ID: 968/FSP 2449.00/22



Functional Safety

Approval ID: 968/FSP 2449.00/22



cULus Listed

Approval ID: E238705

AXL F LPSDO8/3 1F - Safety module



2702171

<https://www.phoenixcontact.com/in/products/2702171>

Classifications

ECLASS

ECLASS-11.0	27242604
ECLASS-12.0	27242604
ECLASS-13.0	27242604

ETIM

ETIM 9.0	EC001599
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c46c2bb2-51c1-41e0-804d-ad04fbcdddc6

AXL F LPSDO8/3 1F - Safety module

2702171

<https://www.phoenixcontact.com/in/products/2702171>



Accessories

AXL F BS F - Bus connector

2688129

<https://www.phoenixcontact.com/in/products/2688129>

Axioline F bus base module for housing type F



ZB 20,3 AXL UNPRINTED - Zack marker strip

0829579

<https://www.phoenixcontact.com/in/products/0829579>



Zack marker strip for Axioline F (device labeling), in 2 x 20.3 mm pitch, unprinted, 25-section, for individual labeling with B-STIFT 0.8, X-PEN, or CMS-P1-PLOTTER

AXL F LPSDO8/3 1F - Safety module

2702171

<https://www.phoenixcontact.com/in/products/2702171>



ZBF 10/5,8 AXL UNPRINTED - Zack Marker strip, flat

0829580

<https://www.phoenixcontact.com/in/products/0829580>



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 10.15 mm, Number of individual labels: 50, text field height: 5 mm, text field width: 10.15 mm

EMT (35X46)R - Insert label

0801604

<https://www.phoenixcontact.com/in/products/0801604>



Insert label, for marking the Axioline F series from Phoenix Contact, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: insert, Number of individual labels: 500, text field height: 46 mm, text field width: 35 mm

AXL F LPSDO8/3 1F - Safety module

2702171

<https://www.phoenixcontact.com/in/products/2702171>



EMT (35X46)R YE - Insert label

0801605

<https://www.phoenixcontact.com/in/products/0801605>



Insert label, for marking the Axioline F series from Phoenix Contact, Roll, yellow, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: insert, Number of individual labels: 500, text field height: 46 mm, text field width: 35 mm

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in