Data sheet

Commercial Art.No.: 78.014.0353.0

modular insert FLE STC 3 69

Modular connector system 3 pole male insert, 630V/40A, crimp connection, turned contacts



Commercial Art.No.	78.014.0353.0
EAN	4015573445970
Order Unit	10

certificates / approvals

Technical data

general

model	pin insert
inflammability class of insulation material acc. with UL94	V0
color	grey
mating cycles	500
pollution degree	3
suitable for modular version	yes
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

connection data

connection type	crimp
number of poles	3
plus switching contacts	0
number of pole for rated current 2	0
number of pole for rated current 3	0
total number of poles (without ground contact)	3
with wire protection	no
protective contact	no

technical data UL/CSA

nominal voltage according to UL/CSA	600 V
nominal current according UL	40 A

nominal current according CSA	35 A
min. conductor cross section flexible wire	1.5 mm²
max. conductor cross section flexible wire	10 mm²
conductor cross section flexible AWG wire	16-8 AWG

model

with housing	no

contacts

contact material	see contacts
surface	silver-plated
contact resistance	≤ 1 mOhm
wire strip length	10 mm

technical data DIN EN 61984


nominal voltage	630 V
nominal voltage face/ground	630 V
nominal current	40 A
rated impulse voltage	8 kV


classification

ECLASS 11	
ECLASS 8.1	27440205
ETIM 9.0	EC000438
ETIM 8.0	EC000438
ETIM 7.0	EC000438
ETIM 6.0	EC000438
ETIM 5.0	EC000438
ETIM 4.0	EC000438
ETIM 3.0	EC000438

product compliance

ROHS conformity status	compliant
REACH-SVHC conformity status	compliant





These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

Weitere Daten siehe Katalog
further data see catalog

Tolerierung nach DIN 7167/Tolerance system acc. to DIN 7167.
(This DIN-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TQM-05/03 ist einzuhalten.
Conformity with Wieland document UU-TQM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1.Verwendung:
First Use:

Blatt/Sheet: 1 von/of 1

/		Werkstoff/Material	2006	Tag/Date	Name
/			gezeichnet/drawn	19.09.	Treschan
/	Maßstab/Scale		geprüft/checked	-	-
/	%		Normgepr. Stand. check	-	-

Zeichnung Nr./Drawing No.: 78.014.0353.0 01K
Index:
Maße in mm/Dimensions are in mm

/ Vol. mm³ Ofl./Surf. mm² Ersatz für/Replacement for: -

Index | Datum / Blatt Date / Sheet
Änderung/Revision

wieland
Elektrische Verbindungen

Type:
Benennung/Title:

MODULEINSATZ_STECKER

module insert - plug
3-polig / 3 pole

QU-PEM-08/91

7801403530001K_4 CADW1044 treschan 2006-09-19T12:31:04 1.000