




Connectors > PCB Connectors > Backplane Connectors > High Speed Backplane Connectors



Number of Positions: 100

Row-to-Row Spacing: 2 mm [.078 in]

Mating Alignment: With

Mating Alignment Type: Polarization

Number of Rows: 10

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board
Backplane Module Type	Center
PCB Connector Type	PCB Mount Receptacle
Shroud Style	Unshrouded

Configuration Features

Backplane Architecture	Traditional Backplane
Stackable	No
Number of Positions	100
Number of Rows	10
Number of Columns	10
PCB Mount Orientation	Right Angle

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------



Signal Characteristics

Number of Differential Pairs per Column	5
---	---

Body Features

Shield Material	Phosphor Bronze
Primary Product Color	Black

Contact Features

Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	.5 µm[19.68 µin]
Contact Shape & Form	Dual Beam
Contact Mating Area Plating Material	Tin (Sn)
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Type	Receptacle
Contact Current Rating (Max)	1.15 A

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	2.1 mm[.055 in][.083 in]

Mechanical Attachment

Guide Hardware	Without
PCB Mount Retention	With
Mating Retention	Without
PCB Mount Retention Type	Action/Compliant Tail
Mating Alignment	With
Mating Alignment Type	Polarization
Connector Mounting Type	Board Mount

Housing Features

Number of Shrouded Sides	0
Housing Material	Polyester - GF
Centerline (Pitch)	2.5 mm[.098 in]

Dimensions

PCB Thickness (Recommended)	1.4 mm
-----------------------------	--------



Connector Width	21.1 mm[.831 in]
PCB Hole Diameter	.05 mm[.002 in]
Connector Height	11.95 mm[.47 in]
Connector Length	25.48 mm[1.003 in]
Row-to-Row Spacing	2 mm[.078 in]

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tube
------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on





requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 5120952-1 HS3 10 Row Header, sequenced, LF	 TE Part # 5120753-1 Z-PACK HS3 HDR ASY 10R 100P,HL	 TE Part # 5120663-1 Z-PACK HS3 SHR ASY 10R 100 P	 TE Part # 6645401-1 Z-PACK HS3 HDR ASY 10R 100P Au /12PdNi
 TE Part # 5120664-2 Z-PACK HS3 HDR ASY 10R 100P	 TE Part # 5120658-1 Z-PACK HS3 HDR ASY 10R 100P	 TE Part # 5120664-1 Z-PACK HS3 HDR ASY 10R 100P	 TE Part # 5120881-1 HS3 PIN SSY, 100 POSN FEED THR
 TE Part # 5120658-2 Z-PACK HS3 HDR ASY 10R 100P	 TE Part # 5120909-1 10 ROW HS3 PIN ASSEMBLY		

Also in the Series | Z-PACK HS3

 Connector Caps & Covers(2)	 Connector Hardware(1)	 High Speed Backplane Connectors(39)
---	---	--

Customers Also Bought





TE Part #1825264-1
MSS420004=4PDT SL SW AG




TE Part #87756-6
MOD IV RECP PLTD SN



TE Part #66504-9
SOCKET CONTACT, 20 DF



TE Part #5352068-9
Z-PACK/A RAF 110P



TE Part #5745833-5
CABLE CLAMP KIT,SZ 3




TE Part #66506-9
PIN CONTACT, 20 DF



TE Part #1658685-1
HDP-22,RCPT,SIZE 5,78 POSN



TE Part #1888810-2
EMI/Dust Cover,XFP And QSFP



TE Part #806250-000
202C611-51-0

Documents

Product Drawings
ZP HS3 DB 10R REC 100P CT PD
English

CAD Files
3D PDF

English

Customer View Model
ENG_CVM_5120790-1_O1.2d_dxf.zip

English

Customer View Model
ENG_CVM_5120790-1_O1.3d_igs.zip

English

Customer View Model
ENG_CVM_5120790-1_O1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



High Speed Backplane Connectors catalog - Z-PACK HS3 Connector

English

Product Specifications

Application Specification

English