

ZLLS2000


40V SILICON HIGH CURRENT LOW LEAKAGE SCHOTTKY DIODE

SUMMARY

Schottky Diode $V_R = 40V$; $I_F = 2.2A$; $I_R = 40\mu A$

DESCRIPTION

This compact SOT23-6 packaged Schottky diode offers users an excellent performance combination comprising high current operation, extremely low leakage and low forward voltage ensuring suitability for applications requiring efficient operation at higher temperatures (above 85°C) see Operational Efficiency chart on page 4.



Key benefits:

Performance capability equivalent to much larger packages

Improved circuit efficiency & power levels

PCB area savings

FEATURES

- Low equivalent on resistance
- Extremely low leakage (40 μA @30V)
- High current capability ($I_F = 2.2A$)
- Low V_F , fast switching Schottky
- SOT23-6 package
- ZLLS2000 complements low temperature equivalent ZHCS2000
- Package thermally rated to 150°C

APPLICATIONS

- DC - DC converters
- Strobes
- Mobile phones
- Charging circuits
- Motor control

ORDERING INFORMATION

DEVICE	REEL (inches)	TAPE WIDTH (mm)	QUANTITY PER REEL
ZLLS2000TA	7	8mm embossed	3000 units
ZLLS2000TC	13	8mm embossed	10000 units


DEVICE MARKING

LL20

Cathode



Anode



Top view

ZLLS2000

ABSOLUTE MAXIMUM RATINGS

PARAMETER	SYMBOL	VALUE	UNIT	
Schottky Diode				
Continuous reverse voltage	V_R	40	V	
Forward current	I_F	2.2	A	
Peak repetitive forward current Rectangular pulse duty cycle	I_{FPK}	3.55	A	
Non repetitive forward current	I_{FSM}	$t \leq 100 \mu s$	36	A
		$t \leq 10 ms$	12	A
Package				
Power dissipation at $T_{amb}=25^\circ C$ single die continuous single die measured at $t < 5$ secs	P_D	1.1	W	
		1.71	W	
Storage temperature range	T_{stg}	-55 to +150	$^\circ C$	
Junction temperature	T_j	150	$^\circ C$	

THERMAL RESISTANCE


PARAMETER	SYMBOL	VALUE	UNIT
Junction to ambient (a)	$R_{\theta JA}$	113	$^\circ C/W$
Junction to ambient (b)	$R_{\theta JA}$	73	$^\circ C/W$

Notes

- (a) For a device surface mounted on 25mm x 25mm FR4 PCB with high coverage of single sided 1oz copper, in still air conditions.
- (b) For a device surface mounted on FR4 PCB measured at $t < 5$ secs.

ZLLS2000

TYPICAL CHARACTERISTICS



ZLLS2000


ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^{\circ}\text{C}$ unless otherwise stated)

SCHOTTKY DIODE CHARACTERISTICS						
PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	CONDITIONS
Reverse breakdown voltage	$V_{(BR)R}$	40			V	$I_R = 1\text{mA}$
Forward voltage	V_F		260	-	mV	$I_F = 50\text{mA}^*$
			290	-	mV	$I_F = 100\text{mA}^*$
			322	-	mV	$I_F = 250\text{mA}^*$
			345	370	mV	$I_F = 500\text{mA}^*$
			395	430	mV	$I_F = 1000\text{mA}^*$
			440	490	mV	$I_F = 1500\text{mA}^*$
			475	540	mV	$I_F = 2000\text{mA}^*$
			550	640	mV	$I_F = 3000\text{mA}^*$
Reverse current	I_R		25	40	μA mA	$V_R = 30\text{V}$ $V_R = 30\text{V}, T_a = 85^{\circ}\text{C}$
Diode capacitance	C_D		65		pF	$f = 1\text{MHz}, V_R = 30\text{V}$
Reverse recovery time	t_{rr}		6		ns	Switched from $I_F = 500\text{mA}$ to $V_R = 5.5\text{V}$
Reverse recovery charge	Q_{rr}		685		pC	Measured @ $I_R = 50\text{mA}$. $di / dt > 500\text{mA} / \text{ns}$. $R_{source} = 6\Omega; R_{load} = 10\Omega$

*Measured under pulsed conditions. Pulse width=300 μs . Duty cycle $\leq 2\%$


Operational efficiency chart

The operational efficiency chart indicates the beneficial use of the ZLLS series diodes in applications requiring higher voltage, higher temperature operation. Circuits requiring low voltage low temperature operation will benefit from using Zetex low V_F ZHCS series diodes.



Operational Efficiency Example

TYPICAL CHARACTERISTICS



ZLLS2000

Definitions

Product change

Zetex Semiconductors reserves the right to alter, without notice, specifications, design, price or conditions of supply of any product or service. Customers are solely responsible for obtaining the latest relevant information before placing orders.

Applications disclaimer

The circuits in this design/application note are offered as design ideas. It is the responsibility of the user to ensure that the circuit is fit for the user's application and meets with the user's requirements. No representation or warranty is given and no liability whatsoever is assumed by Zetex with respect to the accuracy or use of such information, or infringement of patents or other intellectual property rights arising from such use or otherwise. Zetex does not assume any legal responsibility or will not be held legally liable (whether in contract, tort (including negligence), breach of statutory duty, restriction or otherwise) for any damages, loss of profit, business, contract, opportunity or consequential loss in the use of these circuit applications, under any circumstances.

Life support

Zetex products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Zetex Semiconductors plc. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body
or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions
for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Reproduction

The product specifications contained in this publication are issued to provide outline information only which (unless agreed by the company in writing) may not be used, applied or reproduced for any purpose or form part of any order or contract or be regarded as a representation relating to the products or services concerned.

Terms and Conditions

All products are sold subjects to Zetex' terms and conditions of sale, and this disclaimer (save in the event of a conflict between the two when the terms of the contract shall prevail) according to region, supplied at the time of order acknowledgement.

For the latest information on technology, delivery terms and conditions and prices, please contact your nearest Zetex sales office.

Quality of product

Zetex is an ISO 9001 and TS16949 certified semiconductor manufacturer.

To ensure quality of service and products we strongly advise the purchase of parts directly from Zetex Semiconductors or one of our regionally authorized distributors. For a complete listing of authorized distributors please visit: www.zetex.com/salesnetwork

Zetex Semiconductors does not warrant or accept any liability whatsoever in respect of any parts purchased through unauthorized sales channels.

ESD (Electrostatic discharge)

Semiconductor devices are susceptible to damage by ESD. Suitable precautions should be taken when handling and transporting devices. The possible damage to devices depends on the circumstances of the handling and transporting, and the nature of the device. The extent of damage can vary from immediate functional or parametric malfunction to degradation of function or performance in use over time. Devices suspected of being affected should be replaced.

Green compliance

Zetex Semiconductors is committed to environmental excellence in all aspects of its operations which includes meeting or exceeding regulatory requirements with respect to the use of hazardous substances. Numerous successful programs have been implemented to reduce the use of hazardous substances and/or emissions.

All Zetex components are compliant with the RoHS directive, and through this it is supporting its customers in their compliance with WEEE and ELV directives.

Product status key:

"Preview"Future device intended for production at some point. Samples may be available

"Active"Product status recommended for new designs

"Last time buy (LTB)"Device will be discontinued and last time buy period and delivery is in effect

"Not recommended for new designs"Device is still in production to support existing designs and production

"Obsolete"Production has been discontinued

Datasheet status key:

"Draft version" This term denotes a very early datasheet version and contains highly provisional information, which may change in any manner without notice.


"Provisional version" This term denotes a pre-release datasheet. It provides a clear indication of anticipated performance. However, changes to the test conditions and specifications may occur, at any time and without notice.

"Issue" This term denotes an issued datasheet containing finalized specifications. However, changes to specifications may occur, at any time and without notice.




ZLLS2000

PACKAGE DIMENSIONS



PAD LAYOUT DETAILS



DIM	Millimeters	
	Min.	Max.
A	0.90	1.45
A1	0.00	0.15
A2	0.90	1.30
b	0.20	0.50
C	0.09	0.26
D	2.70	3.10
E	2.20	3.20
E1	1.30	1.80
L	0.10	0.60
e	0.95 REF	
e1	1.90 REF	
θ	0°	30°

© Zetex Semiconductors plc 2007

Europe	Americas	Asia Pacific	Corporate Headquarters
Zetex GmbH Kustermann-Park Balanstraße 59 D-81541 München Germany Telefon: (49) 89 45 49 49 0 Fax: (49) 89 45 49 49 49 europa.sales@zetex.com	Zetex Inc 700 Veterans Memorial Hwy Hauppauge, NY 11788 USA Telephone: (1) 631 360 2222 Fax: (1) 631 360 8222 usa.sales@zetex.com	Zetex (Asia) Ltd 3701-04 Metroplaza Tower 1 Hing Fong Road, Kwai Fong Hong Kong Telephone: (852) 26100 611 Fax: (852) 24250 494 asia.sales@zetex.com	Zetex Semiconductors plc Zetex Technology Park Chadderton, Oldham, OL9 9LL United Kingdom Telephone (44) 161 622 4444 Fax: (44) 161 622 4446 hq@zetex.com

These offices are supported by agents and distributors in major countries world-wide.

This publication is issued to provide outline information only which (unless agreed by the Company in writing) may not be used, applied or reproduced for any purpose or form part of any order or contract or be regarded as a representation relating to the products or services concerned. The Company reserves the right to alter without notice the specification, design, price or conditions of supply of any product or service.

For the latest product information, log on to www.zetex.com

ISSUE 4 - APRIL 2007