



Connectors > Pluggable IO Connectors & Cages



Form Factor: **QSFP28/56**
Pluggable I/O Product Type: **Cage**
Sealable: **Yes**
Circuit Application: **Signal**
Number of Ports: **3**

Features

Product Type Features

Cage Type	Ganged
Form Factor	QSFP28/56
Pluggable I/O Product Type	Cage
Sealable	Yes

Configuration Features

Number of Rear EONs per Port Column	1
Number of Ports	3
Port Matrix Configuration	1 x 3

Contact Features

PCB Contact Termination Area Plating Material	Tin
---	-----

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	2.05 mm[.081 in]

Housing Features

--	--



Cage Material	Nickel Silver
---------------	---------------

Dimensions

PCB Thickness (Recommended)	2.2 mm[.086 in]
-----------------------------	-----------------

Operation/Application

Pluggable I/O Applications	SFP+ Stacked Belly-to-Belly
Heat Sink Compatible	Yes
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Other

Included Lightpipe	No
EMI Containment Feature Type	Customer Applied Gasket

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits





as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 1551920-2 zQSFP+ connector assembly	 TE Part # CAT-Q17-N490325 QSFP56 to QSFP56 Cable Assembly: 30 AWG	 TE Part # CAT-Q17-N490333 QSFP56-Four SFP56 Cable Assembly: 26 AWG	 TE Part # CAT-C11-N490333 QSFP28-Four SFP+ Cable Assembly: 30 AWG
 TE Part # CAT-C11-N49 QSFP28-Two QSFP28 Cable Assembly: 30 AWG	 TE Part # CAT-C11-N490325 QSFP28-Four SFP+ Cable Assembly: 26 AWG	 TE Part # CAT-C11-Z8 QSFP28 to QSFP28 Cable Assembly: 26 AWG	 TE Part # CAT-Q17-N49033 QSFP56-Two QSFP56 Cable Assembly: 30 AWG
 TE Part # CAT-C11-Q17 QSFP56 to QSFP56 Cable Assembly: 26 AWG	 TE Part # 1888810-2 EMI/Dust Cover,XFP And QSFP	 TE Part # CAT-C11-Z806726 QSFP28 to QSFP28 Cable Assembly: 30 AWG	 TE Part # CAT-Q17-N49011 QSFP56-Four SFP56 Cable Assembly: 30 AWG

Also in the Series | zQSFP+/QSFP28

 Pluggable I/O Cable Assemblies(78)	 Pluggable IO Connectors & Cages(424)	 QSFP, QSFP+ & zQSFP+(424)
---	--	--

Customers Also Bought



Documents

Product Drawings
1x3 Cage Assy, Bhnd Bezel, QSFP28
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2173238-1_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_2173238-1_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_2173238-1_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages
QSFP28/56 and zQSFP+ Interconnects
English

Product Specifications
Terminating AMP MTEI Connector
English
Application Specification
English



Application Specification

English