

Product data sheet

Specifications



Repacked Switch and socket-outlet,
Mureva Styl, complete product, 2P +
E, 10AX, French IP55, anthracite

MUR36025W



**This repacked option saves 1.058 over the
standard condition**

Main

Range	Mureva Styl
Product or component type	Switch and socket-outlet
Device presentation	Complete product
Colour tint	Anthracite (RAL 7016)
Main colour tint	Anthracite

Complementary

Device mounting	Surface
Material	PC (polycarbonate) Brass
Technology type	Electromechanical
Number of rocker	1
Switch function	1-pole 2-way
Outlet poles configuration	2P + E
Outlet standard description	Pin earth
Outlet standard deviation	French
Installation direction	Vertical
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Rated current	10 AX
Height	147 mm
Width	76 mm
Depth	64 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Quality labels	CE EAC NF
IP degree of protection	IP55
IK degree of protection	IK08

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.400 cm
Package 1 Width	7.600 cm
Package 1 Length	14.700 cm
Package 1 Weight	240.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	10
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.704 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

1 kg CO2 eq.

Use Better



Materials and Substances

SCIP Number

C6de3800-7220-4403-a6a2-26e1f05e3f4b

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins