

Product data sheet

Specifications



Repacked, auxiliary contact, Acti9
A9A, iSD+OF, 2 C/O, 2mA to
100mA, 24VAC to 250VAC, 24VDC
to 220VDC, top and bottom
connection

A9A26919W



This repacked option saves 0.351 over the
standard condition

Main

range of product	Acti9
Product or component type	OC and fault contact
Device short name	iSD+OF
Signal contacts composition	2 C/O
[In] rated current	2...100 mA at 24...240 V, AC 50/60 Hz 2...100 mA at 24 V, DC 2...100 mA at 48 V, DC 2...100 mA at 60 V, DC 2...100 mA at 130 V, DC 2...100 mA at 220 V, DC
9 mm pitches	1
Standards	EN/IEC 60947-5-1 EN/IEC 60947-5-4 GB/T 14048.5 GB/T 14048.17
Product certifications	CE UKCA
Quality labels	EAC CCC

Complementary

Range compatibility	Acti9 iSW-NA Acti9 iC60 Acti9 iLD Acti9 ARA Acti9 RCA Acti9 IDPN Vigi Acti9 iC40 Acti9 iCVm40 Acti9 iCVr40 Acti9 iDDm40
Operating mode	Daisy chain up to 100 devices
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	4 kV
Local signalling	Mechanical indicator
Mounting mode	Clip-on
Mounting location	Left side of circuit-breaker
Mounting support	DIN rail

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Comb busbar and distribution block compatibility	NO
Height	90 mm
Width	9 mm
Depth	73 mm
Product weight	40 g
Colour	White
Connections - terminals	Screw clamp terminal (top and bottom): 1 cable(s) 1...4 mm² - rigid Screw clamp terminal (top and bottom): 1 cable(s) 0.5...2.5 mm² - flexible Screw clamp terminal (top and bottom): 2 cable(s) 2.5 mm² - rigid Screw clamp terminal (top and bottom): 2 cable(s) 1.5 mm² - flexible with ferrule
Wire stripping length	10 mm
Tightening torque	1 N.m top or bottom

Environment

IP degree of protection	IP20
Pollution degree	3
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.300 cm
Package 1 Width	7.500 cm
Package 1 Length	9.000 cm
Package 1 Weight	44.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	36
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.772 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.4 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

9da5f8d9-d60f-424a-bb30-a856a097686c

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins