




TE Internal #: 172213-4
Housing, Plug, Wire-to-Board, 4 Position, 2.5 mm [.098 in]
Centerline, Crimp, 1 Row, Natural, Wire & Cable, Power & Signal,
Panel Mount
[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**
Connector & Housing Type: **Plug**
Connector System: **Wire-to-Board**
Number of Positions: **4**
Centerline (Pitch): **2.5 mm [.098 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	1

Electrical Characteristics

Operating Voltage	350 VDC
-------------------	---------

Body Features

Connector Profile	Standard
Primary Product Color	Natural

Contact Features

--	--



Contact Layout	Inline
Contact Type	Pin
Contact Current Rating (Max)	2 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	With
Mating Retention Type	Lock
PCB Mount Retention	Without
Mating Retention	With
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	Nylon 6/6
Centerline (Pitch)	2.5 mm[.098 in]

Dimensions

Panel Thickness (Recommended)	.81 – 1.6 mm[.032 – .063 in]
Connector Height	8 mm
Connector Length	18.5 mm

Usage Conditions

Operating Temperature Range	-20 – 95 °C[-4 – 203 °F]
-----------------------------	--------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	UL
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Bag
Packaging Quantity	1000

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Melamine (3% in 23412681598) Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 170430-2
EI PIN LP



TE Part # 170376-3
EIS CONN. PIN CONTACT



TE Part # 170429-1
EIS REC CONT 26-20 AWG BR TN



TE Part # 170429-2
EIS REC CONT 26-20 AWG PHOS TN



TE Part # 170429-3
SERIE EI STIFTKONT



TE Part # 170430-1
EI PIN LP 170377-1 LP



TE Part # 170377-2
EIS CONN PIN CONTACT



TE Part # 170377-3
EIS PIN CONT GOLD



TE Part # 170376-1
AMP EI PIN CONTACT



TE Part # 171822-4
EIS REC. HSG 4P-NATURAL



TE Part # 170377-1
EIS CONTACT



TE Part # 170430-3
EIS PIN CONT GOLD LP



TE Part # 170376-2
EI-SRS COSI CONTACT

Customers Also Bought



TE Part #CAT-D486-CH8172
DEUTSCH DTP Housings



TE Part #172211-4
EIS CAP HSG FREE HANG 4P NATUTURAL



TE Part #172213-3
EIS CAP HSG PANEL MOUNT 3P NATUTURAL



TE Part #DRC26-40SB-L011
PLG, 40P, BLK, N, ROUTER CAP, B



TE Part #172213-6
EIS CAP HSG PANEL MOUNT 6P NATUTURAL



TE Part #172213-2
EIS CAP HSG PANEL MOUNT 2P NATUTURAL



TE Part #DT04-12PB-CE07
REC, 12P, BLK, E, ENH KEY, CAP, B



TE Part #DT06-3S-CE14
PLG, 3P, BLK, E, LATCH PROTECT CAP



TE Part #DTHD04-1-4P-E003
REC, 1P, BLK, N, SIZE 4, CAP

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_172213-4_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_172213-4_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_172213-4_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773972-5_EIS_Connectors_Brochure

English

Product Specifications

Crimping of AMP EI Series Connector Contacts

Japanese

Application Specification

Japanese

Agency Approvals

Agency Approval Document

English