



Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**  
Connector & Housing Type: **Receptacle**  
Termination Method to Wire & Cable: **Crimp**  
Connector System: **Cable-to-Cable, Cable-to-Panel**  
Contact Retention Within Housing: **With**

Features

Product Type Features

|                                   |                                |
|-----------------------------------|--------------------------------|
| Connector Product Type            | Housing                        |
| Connector & Housing Type          | Receptacle                     |
| Connector System                  | Cable-to-Cable, Cable-to-Panel |
| Sealable                          | No                             |
| Connector & Contact Terminates To | Wire & Cable                   |

Configuration Features

|                            |    |
|----------------------------|----|
| Number of Signal Positions | 34 |
| Number of Power Positions  | 34 |
| Number of Positions        | 34 |
| Number of Rows             | 4  |

Electrical Characteristics

|                   |         |
|-------------------|---------|
| Operating Voltage | 250 VAC |
|-------------------|---------|

Body Features

|                       |       |
|-----------------------|-------|
| Primary Product Color | Black |
|-----------------------|-------|



Contact Features

|                                  |        |
|----------------------------------|--------|
| Contact Type                     | Socket |
| Contact Retention Within Housing | With   |
| Contact Current Rating (Max)     | 13 A   |

Termination Features

|                                    |       |
|------------------------------------|-------|
| Termination Method to Wire & Cable | Crimp |
|------------------------------------|-------|

Mechanical Attachment

|                          |             |
|--------------------------|-------------|
| Panel Mount Feature      | With        |
| Panel Mount Feature Type | Screw Mount |
| Connector Mounting Type  | Panel Mount |

Housing Features

|                    |                 |
|--------------------|-----------------|
| Housing Material   | Phenolic        |
| Centerline (Pitch) | 3.81 mm[.15 in] |

Dimensions

|                    |                   |
|--------------------|-------------------|
| Row-to-Row Spacing | 4.57 mm[.18 in]   |
| Connector Width    | 19.05 mm[.75 in]  |
| Connector Height   | 50.8 mm[1.999 in] |
| Wire Size          | 30 – 14 AWG       |
| Connector Length   | 23.24 mm[.915 in] |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 150 °C[-67 – 302 °F] |
|-----------------------------|----------------------------|

Operation/Application

|                     |                |
|---------------------|----------------|
| Circuit Application | Power & Signal |
|---------------------|----------------|

Industry Standards

|                        |                               |
|------------------------|-------------------------------|
| Glow Wire Rating       | Standard Part - Not Glow Wire |
| UL Flammability Rating | UL 94V-0                      |

Packaging Features

|                    |        |
|--------------------|--------|
| Packaging Quantity | 85     |
| Packaging Method   | Carton |

Product Compliance

For compliance documentation, visit the product page on TE.com>



|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Wave solder capable to 265°C                                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-201357-1  
MALE BLOCK 34 PL




TE Part # 1-201357-0  
M-SERIES BLOCK,34 POS



TE Part # 201357-1  
MALE BLOCK 34 PL


Also in the Series | AMP M Series



Board-to-Board Jumpers & Shunts(5)




Connector Caps & Covers(14)



Connector Hardware(46)



Connector Strain Relief(13)




PCB Headers & Receptacles(9)



Rack & Panel Connectors(1)



Rectangular Power Connectors(82)




Wire-to-Board Headers & Receptacles (1)

Customers Also Bought



TE Part #557732-001  
CES-4-T1



TE Part #6-1617760-7  
FCB-405-0521M=M83536/5-021M




TE Part #913237-000  
55A1811-20-9-9CS2275




TE Part #201358-1  
MALE BLOCK 50 PL. SER. "M"




TE Part #913237-000  
55A1811-20-9-9CS2275



TE Part #5-1617758-2  
FCB-205-0226M=M83536/2-026M



TE Part #3-1617758-3  
FCB-205-0124M=M83536/1-024M



TE Part #1879639-8  
H4P 14R 0.5% 50PPM



TE Part #200277-2  
FEMALE BLOCK 50 PL.



TE Part #E4050402ATM  
E4050402ATM=RELAY

Documents



Product Drawings

BLOCK,34 POSN,M SERIES

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_200838-2\_BH.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_200838-2\_BH.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_200838-2\_BH.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M\_SERIES\_PIN\_AND\_SOCKET\_CONNECTORS

English

Instruction Sheets

Instruction Sheet (U.S.)

English

20 HVC, 34 AND 50 POSITION SERIES "M" CONNECTOR

English

Agency Approvals

Agency Approval Document

English