

Siemens  
EcoTech



RCBO compact 1 MW 1-pole+N 4.5 kA type A 30 mA C13



Figure similar

| Model  |  |
|--|--|
| product brand name   | SENTRON  |
| product designation  | RCBO   |
| design of the product  | Instantaneous  |
| General technical data   |  |
| number of poles  | 2  |
| number of poles with protection  | 1  |
| design of pole   | 1P+N   |
| tripping characteristic class  | C  |
| mechanical service life (operating cycles) typical   | 10 000   |
| overvoltage category   | 3  |
| degree of pollution  | 2  |
| Voltage  |  |
| type of voltage of the operating voltage   | AC   |
| insulation voltage (U <sub>i</sub> ) rated value   | 253 V  |
| surge voltage resistance rated value   | 4 000 V  |
| surge current resistance at (8/20) $\mu$ s   | 1 kA   |
| tripping fault current rated value   | 30 mA  |
| <ul style="list-style-type: none"> <li>● operational current</li> <li>— at 30 °C rated value</li> <li>— at 40 °C rated value</li> <li>— at 45 °C rated value</li> <li>— at 50 °C rated value</li> <li>— at 55 °C rated value</li> <li>— at 60 °C rated value</li> <li>— at 65 °C rated value</li> <li>— at 70 °C rated value</li> <li>● operational current at AC rated value</li> </ul> | 13 A<br>12.35 A<br>11.96 A<br>11.57 A<br>11.18 A<br>10.79 A<br>10.4 A<br>10.01 A<br>13 A |
| residual current type  | A  |
| Supply voltage   |  |
| supply voltage   |  |
| <ul style="list-style-type: none"> <li>● at AC rated value</li> <li>● for testing equipment minimum</li> </ul>   | 230 V<br>195 V   |
| operating frequency  | 50/60 Hz   |

|   |   |
|---|---|
| supply voltage frequency rated value  | 50 Hz   |
| <b>Protection class</b>   |   |
| <b>protection class IP</b>  | IP20, if the distribution board is installed, with connected conductors |
| <b>Breaking Capacity</b>  |   |
| <b>switching capacity current</b>   |   |
| • according to EN 60898 rated value   | 4.5 kA  |
| • according to IEC 60947-2 rated value  | 5 kA  |
| <b>short-circuit current breaking capacity (I<sub>cn</sub>) according to EN 61009-1 rated value</b> | 4.5 kA  |
| <b>rated residual switching capacity (I<sub>Δm</sub>) according to IEC 61009-1</b>                  | 4.5 kA  |
| <b>energy limitation class</b>  | 3   |
| <b>Dissipation</b>  |   |
| <b>power loss [W]</b>   |   |
| • maximum   | 2.5 W   |
| <b>Product details</b>  |   |
| <b>product feature touch protection</b>   | Yes   |
| product component neutral conductor switching   | Yes   |
| <b>product feature halogen-free</b>   | Yes   |
| <b>product feature silicon-free</b>   | Yes   |
| <b>Connections</b>  |   |
| <b>connectable conductor cross-section solid</b>  |   |
| • minimum   | 0.75 mm <sup>2</sup>  |
| • maximum   | 16 mm <sup>2</sup>  |
| <b>connectable conductor cross-section stranded</b>   |   |
| • minimum   | 0.75 mm <sup>2</sup>  |
| • maximum   | 16 mm <sup>2</sup>  |
| <b>connectable conductor cross-section finely stranded with core end processing</b>                 |   |
| • minimum   | 0.75 mm <sup>2</sup>  |
| • maximum   | 10 mm <sup>2</sup>  |
| <b>tightening torque with screw-type terminals</b>  |   |
| • minimum   | 1.2 N·m   |
| • maximum   | 2 N·m   |
| <b>position of power supply cord</b>  | Either top or bottom  |
| <b>Mechanical Design</b>  |   |
| <b>height</b>   | 90 mm   |
| <b>width</b>  | 18 mm   |
| <b>depth</b>  | 77 mm   |
| <b>installation depth</b>   | 70 mm   |
| <b>number of modular width units</b>  | 1   |
| <b>mounting position</b>  | any   |
| <b>Net Weight</b>   | 125 g   |
| <b>weight with packaging</b>  | 133 g   |
| <b>Environmental conditions</b>   |   |
| <b>influence of the surrounding temperature</b>   | Max. 95% humidity   |
| <b>ambient temperature during operation</b>   |   |
| • minimum   | -25 °C  |
| • maximum   | 45 °C   |
| <b>ambient temperature during storage</b>   |   |
| • minimum   | -40 °C  |
| • maximum   | 75 °C   |
| <b>number of test cycles for environmental testing according to IEC 60068-2-30</b>                  | 28  |
| <b>Approvals Certificates</b>   |   |
| <b>Environmental Product Declaration</b>  |   |
| • global warming potential [CO <sub>2</sub> eq] / during manufacturing                              | 1.32 kg   |
| • global warming potential [CO <sub>2</sub> eq] / during sales                                      | 0.0287 kg   |
| • global warming potential [CO <sub>2</sub> eq] / during operation                                  | 16.6 kg   |
| • global warming potential [CO <sub>2</sub> eq] / after end of life                                 | 0.00156 kg  |

• global warming potential [CO2 eq] / total

17.95026 kg

Environment

General Product Approval



Siemens  
EcoTech



[Environmental Con-  
firmations](#)

[Environmental Con-  
firmations](#)



[Confirmation](#)

General Product Approval

Test Certificates



[Miscellaneous](#)

[Special Test Certificate](#)

other

Dangerous goods



[Confirmation](#)

[Miscellaneous](#)

[Miscellaneous](#)

[Transport Information](#)

### Further information

#### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

#### Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/lowvoltage/catalogs>

#### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SV1313-7KK13>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SV1313-7KK13>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[https://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SV1313-7KK13](https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SV1313-7KK13)

#### CAX-Online-Generator

<https://www.siemens.com/cax>

#### Tender specifications

<https://www.siemens.com/specifications>

#### Characteristic curves

[https://curves.simaris.siemens.com/curves/<mmp\\_prod\\_noCOMP="HAUPT"></mmp\\_prod\\_no>](https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP=)





